



Powering Business Worldwide

AB Parallel Printer Cable (DB25 to Cen36 M/M), 15-ft.

MODEL NUMBER: P606-015



Description

Tripp Lite's 15-ft. A-B parallel printer cable connects computers with a DB25 female parallel port to parallel printers with a Centronics 36 female parallel port. Built to the IEEE 1284 standard to provide superior conductivity and support high-speed bi-directional printing. The cable features nickel plated DB25 male/Cent36 male connectors and gold plated copper contacts for superior conductivity. It is manufactured from superior molded cable with integral strain relief and double shielding for maximum EMI/RFI protection. It contains low-capacitance, impedance matched, twisted-pair conductors that protect against cross-talk and other transmission problems.

Features

- Built to the IEEE 1284 standard to provide superior conductivity and support high-speed bi-directional printing
- Length: 15-ft. Connectors: DB25 male/Cent36 male
- Nickel plated connectors and gold plated copper contacts offer superior conductivity
- Superior molded cable with integral strain relief and double shielding (foil and braid) for maximum EMI/RFI protection
- Low-capacitance impedance matched twisted-pair conductors protect against cross-talk and other transmission problems
- Bi-directional communication allows your printer to broadcast printer error messages back to network computers
- Molded ends with easy-grip textured overmold

Specifications

OVERVIEW	
UPC Code	037332013569
Technology	Parallel
CONNECTIONS	

Highlights

- Built to the IEEE 1284 standard to provide superior conductivity and support high-speed bi-directional printing
- Superior molded cables with integral strain relief and foil-shielding for maximum EMI/RFI protection
- Printer Cables provide superior conductivity and support high-speed bi-directional printing

System Requirements

- Computers with a DB25 Female parallel port
- Parallel printers with a Centronics 36 Female parallel port with high-speed Bi-Directional communication (although not essential).

Package Includes

- 15-ft. AB Parallel Printer Cable DB25M to Cen36M

Side A - Connector 1	DB25 (MALE)
Side B - Connector 1	CENTRONICS 36 (MALE)
PHYSICAL	
Color	Black
Cable Length (ft.)	15
Cable Length (m)	4.57
Shipping Dimensions (hwd / in.)	12.00 x 10.00 x 0.50
Shipping Dimensions (hwd / cm)	30.48 x 25.40 x 1.27
Shipping Weight (lbs.)	0.94
Shipping Weight (kg)	0.43
Unit Dimensions (hwd / in.)	0.000 x 0.000 x 0.000
WARRANTY & SUPPORT	
Product Warranty Period (Worldwide)	Lifetime limited warranty

1000 Eaton Boulevard
Cleveland, OH 44122
United States
<https://tripplite.eaton.com>

© 2024 Eaton. All Rights Reserved.
Eaton is a registered trademark. All other trademarks
are the property of their respective owners.