



Powering Business Worldwide

KVM Switch Cable Kits - 10-ft. AT Cable Kit for KVM Switch B005-008

MODEL NUMBER: P763-010



Highlights

- For use with B005-008 KVM switch when connecting AT style CPU
- Cable has (3) leads: HD15M (video); Din5M (AT style keyboard); DB9M (AT style Mouse)

System Requirements

- An AT computer
- A KVM switch (model # B005-008).

Package Includes

- 10-ft. AT Cable Kit for KVM Switch B005-008 no Audio

Description

Tripp Lite's 10-ft. AT KVM cable kit is designed to connect an AT computer to a B005-008 KVM switch. This premium 3-in-1 cable provides superior performance and cable management. It consists of an AT keyboard cable, a serial mouse cable and an SVGA mini-coax monitor cable all bonded into a single unit. This unique cable has a DIN5 male, a DB9 female and an HD15 male connector on one end with a DB25 male connector on the other end (which connects to the KVM switch). All cables are manufactured from superior molded cable with integral strain relief and foil shielding for maximum EMI/RFI protection. Tripp Lite warrants this product to be free from defects in materials and workmanship for life.

Features

- Connects an at computer to a KVM switch (# B005-008)
- 10-ft. 3-in-1 cable consists of an AT keyboard cable, a serial mouse cable and an SVGA mini-coax monitor cable
- Superior molded cable with integral strain relief and double shielding (foil and braid) for maximum EMI/RFI protection
- Provides superior performance and cable management
- DB25 male connector attaches to the KVM switch
- Molded ends with easy-grip textured overmold
- Tripp Lite warrants this product to be free from defects in materials and workmanship for life
- Monitor cable portion constructed of mini-coax (RGB) and paired video wire to support any VGA/SVGA monitor. Connector: HD15 male
- AT Keyboard cable connector: DIN5 male
- Serial mouse cable connector: DB9 female

Specifications

OVERVIEW	
UPC Code	037332043115
Accessory Type	Cable Kit



Powering Business Worldwide

Accessory Class	KVM Switch Accessories
PHYSICAL	
Cable Length (ft.)	10
Cable Length (m)	3.05
Shipping Dimensions (hwd / in.)	12.50 x 9.50 x 1.50
Shipping Dimensions (hwd / cm)	31.75 x 24.13 x 3.81
Shipping Weight (lbs.)	1.71
Shipping Weight (kg)	0.78
WARRANTY & SUPPORT	
Product Warranty Period (Worldwide)	Lifetime limited warranty

1000 Eaton Boulevard
Cleveland, OH 44122
United States
<https://tripplite.eaton.com>

© 2024 Eaton. All Rights Reserved.
Eaton is a registered trademark. All other trademarks
are the property of their respective owners.