

# PS/2 (3-in-1) Cable Kit for KVM Switch B007-008, 6 ft. (1.83 m)

MODEL NUMBER: P753-006



### **Highlights**

- Connects a PS/2 computer to a B007-008 KVM switch
- Gold plated copper contacts offer superior conductivity
- Double shielding (foil and braid) for maximum EMI/RFI protection

#### **System Requirements**

- A PS/2 computer.
- A PS/2 KVM switch (model # B007-008).

## **Package Includes**

 6-ft. PS2 Super-Flex 3-IN-1 Cable Kit for the B007-008 KVM Switch

#### **Features**

- Connects a PS/2 computer to a B007-008 KVM switch
- KVM Switch side of the cable kit consists of a HD15 Female cable, a PS/2 (MiniDIN6) Mouse cable and a PS/2 (MiniDIN6) Keyboard cable
- Computer side of the cable kit consists of a HD15 Male cable, a PS/2 (MiniDIN6) Male Mouse cable and a PS/2 (MiniDIN6) Keyboard cable
- Innovative, low profile design allows the cable to be incredibly flexible and easy to control
- Gold plated copper contacts offer superior conductivity
- Double shielding (foil and braid) for maximum EMI/RFI protection

# **Specifications**

OVERVIEW		
UPC Code	037332119391	
Accessory Type	Cable Kit	
Technology	PS/2; VGA/SVGA	
Accessory Class	KVM Switch Accessories	
CONNECTIONS		
KVM Switch Side 1	HD15 (Female)	
KVM Switch Side 2	(x2) MiniDIN6 (Male)	
Computer Side 1	HD15 (Male)	
Computer Side 2	(x2) MiniDIN6 (Male)	



PHYSICAL		
Cable Length (ft.)	6	
Cable Length (m)	1.83	
Shipping Dimensions (hwd / in.)	7.00 x 9.00 x 0.50	
Shipping Dimensions (hwd / cm)	17.78 x 22.86 x 1.27	
Shipping Weight (lbs.)	0.50	
Shipping Weight (kg)	0.23	
FEATURES & SPECIFICATIONS		
IP68 Rated	No	
IP20 Rated	No	
STANDARDS & COMPLIANCE		
Product Compliance	RoHS	
WARRANTY & SUPPORT		
Product Warranty Period (Worldwide)	Lifetime limited warranty	

1000 Eaton Boulevard Cleveland, OH 44122 United States https://tripplite.eaton.com © 2024 Eaton. All Rights Reserved. Eaton is a registered trademark. All other trademarks are the property of their respective owners.