



Powering Business Worldwide

KVM Switch Cable Kits - 10-ft. PS2 Cable Kit for KVM Switch

MODEL NUMBER: **P754-010**

Description

Tripp Lite's 10-ft. PS/2 (3-in-1) KVM cable kit is designed to connect a PS/2 computer or a console converter to a KVM switch. This premium 3-in-1 cable provides superior performance and cable management. It consists of 2 PS/2 keyboard/mouse cables and a SVGA mini-coax monitor cable bonded into a single unit. The cable features MiniDIN6 male/male connectors and gold plated HD15M/F connectors. All cables are manufactured from superior molded cable with integral strain relief and foil shielding for maximum EMI/RFI protection. Tripp Lite warrants this product to be free from defects in materials and workmanship for life.

Features

- Connects a PS/2 computer or a console converter to a KVM switch (# B007-008)
- 10-ft. 3-in-1 cable consists of 2 PS/2 keyboard/mouse cables and an SVGA mini-coax monitor cable bonded into a single unit
- Provides superior performance and cable management
- Molded ends with easy-grip textured overmold
- SVGA monitor cable supports any VGA/SVGA monitor
- Gold plated connectors and gold plated copper contacts offer superior conductivity
- Constructed of mini-coax (RGB) and paired video wire
- Superior molded cable with integral strain relief and double shielding (foil and braid) for maximum EMI/RFI protection
- Hi-Resolution cable
- PS/2 keyboard/mouse cables
- Tripp Lite warrants this product to be free from defects in materials and workmanship for life

Highlights

- Molded 3-in-1 cable kit designed for PS/2 applications
- Supports SVGA and VGA applications
- Color coded connectors match input ports on KVM and most CPU's

System Requirements

- A PS/2 computer or a console converter (# B015-000 and B011-000) for a non-PS/2 computer.
- A PS/2 KVM switch (# B007-008).

Package Includes

- 10-ft. PS/2 Cable Kit for KVM Switches

Specifications

OVERVIEW	
UPC Code	037332014917
Accessory Type	Adapter
Technology	PS/2; VGA/SVGA
Accessory Class	KVM Switch Accessories
PHYSICAL	
Color	Black
Cable Length (ft.)	10
Cable Length (m)	3.05
Shipping Dimensions (hwd / in.)	12.75 x 9.75 x 1.50
Shipping Dimensions (hwd / cm)	32.38 x 24.76 x 3.81
Shipping Weight (lbs.)	1.68



Powering Business Worldwide

Shipping Weight (kg)	0.76
WARRANTY & SUPPORT	
Product Warranty Period (Worldwide)	Lifetime limited warranty

1000 Eaton Boulevard
Cleveland, OH 44122
United States
<https://tripplite.eaton.com>

© 2024 Eaton. All Rights Reserved.
Eaton is a registered trademark. All other trademarks
are the property of their respective owners.