


15-Pin SATA Power Y Cable - M/2xF, 18 AWG, 6-in. (15.24 cm)

MODEL NUMBER: P947-06N-2P15



Highlights

- Allows any 2 SATA hard drives to share a single power connection
- Compatible with 2.5 in. and 3.5 in. SATA drives
- Plug-and-play operation makes it easy to connect in seconds

Applications

- Connect 2 SATA drives to a single SATA power supply without having to upgrade the computer power supply

Package Includes

- P947-06N-2P15 15-Pin SATA Power Y Cable - M/2xF, 6 in.

Adds a SATA hard drive to a computer or server when no additional power supply wiring harness connectors are available.

Features

15-Pin Splitter Allows Additional SATA Drive to be Added to a Computer or Server This 15-pin SATA power Y cable allows an additional SATA hard drive to be added to a computer or server when no additional power supply wiring harness connectors are available. Simply unplug a SATA hard drive power cable from the existing SATA hard drive and connect the plug-and-play splitter to the power cable's 15-pin female end. Reconnect the old and new drives with the two new female 15-pin ends. This eliminates the need to upgrade the computer power supply for compatibility with an additional SATA drive.

Specifications

OVERVIEW	
UPC Code	037332185327
Technology	SATA/eSATA
Country/Region	Global
INPUT	
Maximum Input Amps	1.5
CONNECTIONS	
Side A - Connector 1	15 PIN SATA POWER (MALE)
Side B - Connector 1	(2) 15 PIN SATA POWER (FEMALE)
PHYSICAL	
Color	Black; Red; Yellow



Powering Business Worldwide



Number of Conductors	0
Wire Gauge (OD - mm ²)	2.0
Cable Length (ft.)	0.5
Cable Length (m)	0.15
Cable Length (in.)	6
Cable Length (cm)	15.24
Shipping Dimensions (hwd / in.)	0.50 x 4.00 x 5.50
Shipping Dimensions (hwd / cm)	1.27 x 10.16 x 13.97
Shipping Weight (lbs.)	0.06
Shipping Weight (kg)	0.03
FEATURES & SPECIFICATIONS	
IP68 Rated	No
IP20 Rated	No
High Voltage	No
Locking Plug	No
STANDARDS & COMPLIANCE	
Product Compliance	RoHS; REACH
WARRANTY & SUPPORT	
Product Warranty Period (Worldwide)	Lifetime limited warranty

1000 Eaton Boulevard
Cleveland, OH 44122
United States
<https://tripplite.eaton.com>

© 2024 Eaton. All Rights Reserved.
Eaton is a registered trademark. All other trademarks
are the property of their respective owners.