



Tripp Lite
1111 West 35th Street
Chicago, IL 60609 USA
Telephone: +(773) 869 1234
E-mail: saleshelp@tripplite.com

Model #: PR-EZ1

Wireless Presentation Remote Ideal for Conference Rooms, Boardrooms and Classrooms

Highlights



- Keyspan wireless presentation remote designed to work with PowerPoint, Keynote, Adobe Director, etc.
- 60+ ft. RF range
- Laser pointer
- Audio controls

Description

Keyspan-by-Tripp Lite's Easy Presenter Remote Control provides complete PowerPoint and Keynote control -- including audio control -- plus a laser pointer. It's feature set, simplicity and affordability make it an attractive solution for presenters in business and education.

System Requirements

- Windows:
An available USB port;
Windows 98SE/Me/2000/XP/Windows 7
- Mac OS:
An available USB port;
Mac OS 9.1 or later;
Mac OS X (10.1.5 or later);
Mac OS X (10.6.2)
Requires Mac OS X (10.3 or later) for volume control;
Requires Mac OS X (10.3 or later) and installation of driver to start PowerPoint or Keynote using the F5 button on the remote
- Presentation Software: This remote control is designed for use with PowerPoint and Keynote. It will also work with other presentation programs that use the same keystrokes as PowerPoint. The remote supports both Slide Show view and Presenter view within PowerPoint.
- Multi-Media Software: Volume control buttons adjust system volume on a PC or Mac.
- Projectors: This remote is compatible with all brands of projectors.

Package Includes

- USB Receiver
- Remote
- Remote's Battery (type CR2025)
- Travel Pouch
- Printed Quick Start

Features

- RF Connectivity: Works to 60 ft or more -- even through walls and furniture
- Laser Pointer: Highlight details of your presentation with ease

- Audio Control: Volume and mute buttons control sound
- Plug & Play: No software to install, just plug it in and it works within seconds
- Travel Pouch: Convenient for carrying the remote and receiver
- 1-Year Limited Warranty

Buttons on the Remote:

- Launch presentation (F5)
- Slide forward
- Slide back
- Black screen
- Quit presentation (ESC)
- Volume up
- Volume down
- Mute
- Laser pointer

Button names - associated keystrokes - actions:

- Previous Slide (Left Triangle Button) - Page Up - Moves to previous slide in slideshow
- Next Slide (Right Triangle Button) - Page - Moves to next slide in slideshow
- Volume Up (Up Triangle Button) - System Volume Up Key - Raises the volume level on your computer
- Volume Down (Down Triangle Button) - System Volume Down Key - Lowers the volume level on your computer
- Mute (Speaker Button) - System Mute Key - Mutes all sounds on your computer
- Black Screen (Black Square Button) - B - Blacks screen during a slideshow. Press again to un-black screen
- F5 - F5 -Starts slideshow mode. NOTE for Mac Users: Install optional software to enable F5 to start slideshow mode in PowerPoint/Keynote (See "Help & Downloads" tab)
- ESC - ESC - Stop slideshow
- Laser Button (Red Circle Button) - None or n/a - Press to turn on laser pointer

Specifications

OVERVIEW	
Signal Range (ft.)	60
Model Frequency	433 Mhz
Laser Pointer	Class 2; Maximum output = 1 mW, wavelength = 650 nm
PRODUCT OVERVIEW	
Product Overview	Keyspan-by-Tripp Lite Easy Presenter Remote Control
PHYSICAL	
Color	White
WARRANTY	
Product Warranty Period (U.S., Canada & Puerto Rico)	1-year limited warranty

More information, including related products, owner's manuals, and additional technical specifications, can be found online at www.triplite.com/en/products/model.cfm?txtModelID=3902.

Copyright © 2012 Tripp Lite. All rights reserved. All trademarks are the sole property of their respective owners. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Photos may differ slightly from final products.