



4U UPS Replacement 192VDC Battery Cartridge (1 Set of 16) for Select SmartOnline UPS

MODEL NUMBER: RBC5-192



Description

These premium UPS replacement battery cartridges breathe new life into UPS systems suffering from expired or weak internal batteries. Each replacement battery cartridge is carefully screened and certified to meet or exceed original specifications and ships ready for installation into your UPS system. Reusable packaging holds expired batteries for recycling center delivery. See the UPS replacement battery web page to confirm compatibility and quantity required.

Compatible with models SU5000RT4UHV, SU5000RT4UTF, SU6000RT4UHV, SU6000RT4UHVG, SU6000RT4UHVHW, SU6000RT4UTF, SU6000RT4UTFHW, SU6000RT4UHVPM and other UPS products specifying the use of this replacement battery cartridge

Features

- · Restores UPS runtime performance to original specifications
- · Comes pre-assembled and ready for installation
- Reusable packaging holds expired batteries for recycling center delivery

Specifications

| OVERVIEW | |
|--------------------------|---|
| UPC Code | 037332154576 |
| BATTERY | |
| DC System Voltage (VDC) | 192 |
| Included Battery Set | Contains (16) 12V 5.5AH sealed lead acid batteries |
| Typical Battery Lifespan | 3 to 5 years, depending on UPS operating conditions |
| PHYSICAL | |
| Rack Height | 4U |

Highlights

- Certified premium battery cartridge
- Pre-assembled and wired battery kit offers simple installation
- Rugged leakproof construction
- Maintenance free
- Wide operating temperature range

Package Includes

 Set of 16 pre-wired batteries ready to install





| Minimum Required Rack Depth (cm) | 22.86 |
|--|---------------------------|
| Minimum Required Rack Depth (inches) | 9 |
| Shipping Dimensions (hwd / in.) | 11.30 x 19.30 x 15.30 |
| Shipping Dimensions (hwd / cm) | 28.70 x 49.02 x 38.86 |
| Shipping Weight (lbs.) | 69.00 |
| Shipping Weight (kg) | 31.30 |
| Unit Dimensions (hwd / in.) | 8.350 x 7.090 x 5.510 |
| Unit Dimensions (hwd / cm) | 21.2 x 18 x 14 |
| Unit Weight (lbs.) | 63.9300 |
| Unit Weight (kg) | 29.00 |
| ENVIRONMENTAL | |
| Relative Humidity | 0-95% non-condensing |
| STANDARDS & COMPLIANCE | |
| Product Compliance | RoHS |
| WARRANTY & SUPPORT | |
| Product Warranty Period (U.S. & Canada) | 18-month limited warranty |
| Product Warranty Period (International) | 1-year limited warranty |
| Product Warranty Period (Mexico) | 1-year limited warranty |
| Product Warranty Period (Puerto Rico) | 1-year limited warranty |

1000 Eaton Boulevard Cleveland, OH 44122 United States https://tripplite.eaton.com © 2024 Eaton. All Rights Reserved. Eaton is a registered trademark. All other trademarks are the property of their respective owners.