



UPS Replacement 36VDC Battery Cartridge for Select SLT UPS

MODEL NUMBER: RBC36-SLT



Description

Premium UPS replacement battery cartridges breathe new life into UPS systems suffering from expired or weak internal batteries. Each replacement battery cartridge is carefully screened and certified to meet or exceed original specifications, and ships ready for installation into your UPS system. Reusable packaging holds expired batteries for recycling center delivery. See the UPS replacement battery web page to confirm compatibility and quantity required.

Compatible with SMART1500, SMART1500SLT, SMX1500SLT (versions with pre-assembled threebattery cartridges only; see compatibility listing for non-assembled battery versions)

Features

- Restores UPS runtime performance to original specifications
- Comes pre-assembled and ready for installation
- Reusable packaging holds expired batteries for recycling center delivery

Specifications

OVERVIEW		
UPC Code	037332127136	
BATTERY		
DC System Voltage (VDC)	36	
Included Battery Set	Contains (3) 12V 9AH sealed lead acid batteries	
Typical Battery Lifespan	3-5 years, depending on UPS operating conditions	
PHYSICAL		
Shipping Dimensions (hwd / in.)	4.60 x 6.50 x 11.40	
Shipping Dimensions (hwd / cm)	11.68 x 16.51 x 28.96	

Highlights

- Certified premium battery cartridge
- Pre-assembled and wired battery kit offers simple installation
- Rugged leak-proof construction
- Maintenance free
- Wide operating temperature range

Package Includes

 One pre-assembled battery pack consisting of three 12V batteries





Shipping Weight (lbs.)	19.30	
Shipping Weight (kg)	8.75	
Unit Dimensions (hwd / in.)	4.000 x 6.000 x 7.500	
Unit Dimensions (hwd / cm)	10.16 x 15.2 x 19.1	
Unit Weight (lbs.)	18.8	
Unit Weight (kg)	8.53	
ENVIRONMENTAL		
Relative Humidity	0-95% NON-CONDENSING	
Operating Elevation	0-10000 ft. (0-3000 m)	
Storage Elevation (ft.)	0-50,000 FEET	
Storage Elevation (m)	0 - 15,200 m	
STANDARDS & COMPLIANCE		
Product Compliance	RoHS	
WARRANTY & SUPPORT		
Product Warranty Period (U.S. & Canada)	18-month limited warranty	
Product Warranty Period (International)	1-year limited warranty	
Product Warranty Period (Mexico)	1-year limited warranty	
Product Warranty Period (Puerto Rico)	1-year limited warranty	

1000 Eaton Boulevard Cleveland, OH 44122 United States https://tripplite.eaton.com © 2024 Eaton. All Rights Reserved. Eaton is a registered trademark. All other trademarks are the property of their respective owners.