



Powering Business Worldwide

# UPS Replacement Battery Cartridge for select APC UPS, 8.1-lbs.

MODEL NUMBER: RBC4A



### Highlights

- Up to 30% longer runtime than basic replacements
- OEM certified premium batteries
- Rugged, leakproof construction
- Maintenance-free
- Wide operating temperature range

### Package Includes

- UPS battery replacement cartridge
- Instruction manual with installation, recycling and warranty information

### Description

Tripp Lite's premium UPS replacement battery cartridges breathe new life into UPS systems suffering from expired or weak internal batteries. Each replacement battery set is carefully configured to meet or exceed all of the original manufacturer specifications and ships pre-assembled and ready for installation into your UPS system. Reusable packaging holds expired batteries for recycling center delivery. Compatible with select UPS systems from APC and other major brands See Tripp Lite's UPS replacement battery page to confirm compatibility and quantity required.

### Features

- Restores your UPS to its original runtime specifications
- Comes pre-assembled and ready for installation into your UPS system
- Reusable packaging holds expired batteries for recycling center delivery
- Compatible with many brands and models, including APC models BP650, BP650PNP, BP650C, SUVS650, BP650S, SU620NET and BK650M (date code of 9829 or above)

## Specifications

OVERVIEW	
UPC Code	037332118400
BATTERY	
Typical Battery Lifespan	3 - 5 years, depending on host UPS operating conditions
PHYSICAL	
Shipping Dimensions (hwd / in.)	6.00 x 7.50 x 12.00
Shipping Dimensions (hwd / cm)	15.24 x 19.05 x 30.48
Shipping Weight (lbs.)	10.00



Powering Business Worldwide

Shipping Weight (kg)	4.54
Unit Dimensions (hwd / in.)	3.900 x 3.700 x 5.900
Unit Dimensions (hwd / cm)	9.4 x 9.7 x 14.9
Unit Weight (lbs.)	8.1
Unit Weight (kg)	3.67
<b>ENVIRONMENTAL</b>	
Relative Humidity	0 - 95% non-condensing
Operating Elevation	0 - 10,000
Storage Elevation (ft.)	0 - 50,000
Storage Elevation (m)	0 - 15,200 m
<b>WARRANTY &amp; SUPPORT</b>	
Product Warranty Period (U.S. & Canada)	18-month limited warranty
Product Warranty Period (International)	1-year limited warranty
Product Warranty Period (Mexico)	1-year limited warranty
Product Warranty Period (Puerto Rico)	1-year limited warranty

1000 Eaton Boulevard  
Cleveland, OH 44122  
United States  
<https://tripplite.eaton.com>

© 2024 Eaton. All Rights Reserved.  
Eaton is a registered trademark. All other trademarks  
are the property of their respective owners.