



2U UPS Replacement 48VDC Battery Cartridge (2 Sets of 4) for Select UPS systems

MODEL NUMBER: RBC58-2U



Highlights

- Certified premium battery cartridge
- Pre-assembled and wired battery kit offers simple installation
- Rugged leakproof construction
- Maintenance free
- Wide operating temperature range

Package Includes

 Two pre-assembled battery cartridges, each consisting of 4 pre-wired and connectorized 12V batteries

Description

These premium UPS replacement battery cartridges breathe new life into UPS systems suffering from expired or weak internal batteries. Each replacement battery cartridge is carefully screened and certified to meet or exceed original specifications and ships ready for installation into your UPS system. Reusable packaging holds expired batteries for recycling center delivery. See the UPS replacement battery web page to confirm compatibility and quantity required.

COMPATIBLE WITH MODELS SMART3000RMXL2U and other UPS systems recommending this preassembled replacement battery kit

Features

- Restores UPS runtime performance to original specifications
- Comes pre-assembled and ready for installation
- · Reusable packaging holds expired batteries for recycling center delivery

Specifications

OVERVIEW		
UPC Code	037332151780	
BATTERY		
DC System Voltage (VDC)	48	
Included Battery Set	Contains (8) 12V 5AH sealed lead acid batteries	
Typical Battery Lifespan	3 to 5 years, depending on UPS operating conditions	
PHYSICAL		
Rack Height	2U	
Minimum Required Rack Depth (cm)	45.72	





Minimum Required Rack Depth (inches)	18
Shipping Dimensions (hwd / in.)	5.30 x 17.40 x 12.30
Shipping Dimensions (hwd / cm)	13.46 x 44.20 x 31.24
Shipping Weight (lbs.)	37.00
Shipping Weight (kg)	16.78
Unit Dimensions (hwd / in.)	2.950 x 8.900 x 14.490
Unit Dimensions (hwd / cm)	7.5 x 22.6 x 36.8
Unit Weight (lbs.)	30.4
Unit Weight (kg)	13.79
ENVIRONMENTAL	
Relative Humidity	0-95% non-condensing
STANDARDS & COMPLIANCE	
Product Compliance	RoHS
WARRANTY & SUPPORT	
Product Warranty Period (U.S. & Canada)	18-month limited warranty
Product Warranty Period (International)	1-year limited warranty
Product Warranty Period (Mexico)	1-year limited warranty
Product Warranty Period (Puerto Rico)	1-year limited warranty

1000 Eaton Boulevard Cleveland, OH 44122 United States https://tripplite.eaton.com © 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark. All other trademarks are the property of their respective owners.