

2U UPS Replacement 24VDC Battery Cartridge (1 Set of 2) for Select SmartPro UPS

MODEL NUMBER: RBC92-2U



Highlights

- Certified premium battery cartridge
- Pre-assembled and wired battery kit offers simple installation
- Rugged leakproof construction
- Maintenance free
- Wide operating temperature range

Package Includes

- Pre-assembled battery pack consisting of 2 12V batteries designed to fit select 24V rack-mount SmartPro and SmartOnline models

Description

Premium UPS replacement battery cartridges breathe new life into UPS systems suffering from expired or weak internal batteries. Each replacement battery cartridge is carefully screened and certified to meet or exceed original specifications and ships ready for installation. Reusable packaging holds expired batteries for recycling center delivery. See the UPS replacement battery web page to confirm compatibility and quantity required.

COMPATIBLE WITH SELECT VERSIONS OF SMART750RML2U (LED version only), SMART1000RM2U (LED version only), SMX1000RT2U (LED version only), SU750RTL2U, SU1000RTL2Ua AND OTHER MODELS RECOMMENDING THIS REPLACEMENT BATTERY CARTRIDGE.

Features

- Restores UPS runtime performance to original specifications
- Comes pre-assembled and ready for installation
- Reusable packaging holds expired batteries for recycling center delivery

Specifications

OVERVIEW	
UPC Code	037332121202
BATTERY	
DC System Voltage (VDC)	24
Included Battery Set	Contains (2) 12V 9AH sealed lead acid batteries
Typical Battery Lifespan	3 to 5 years, depending on UPS operating conditions
PHYSICAL	



Powering Business Worldwide



Rack Height	2U
Minimum Required Rack Depth (cm)	25.40
Minimum Required Rack Depth (inches)	10
Shipping Dimensions (hwd / in.)	3.00 x 6.80 x 11.80
Shipping Dimensions (hwd / cm)	7.62 x 17.27 x 29.97
Shipping Weight (lbs.)	13.20
Shipping Weight (kg)	5.99
Unit Dimensions (hwd / in.)	2.750 x 8.000 x 6.500
Unit Dimensions (hwd / cm)	7 x 20.3 x 16.5
Unit Weight (lbs.)	12.6
Unit Weight (kg)	5.72
STANDARDS & COMPLIANCE	
Product Compliance	RoHS
WARRANTY & SUPPORT	
Product Warranty Period (U.S. & Canada)	18-month limited warranty
Product Warranty Period (International)	1-year limited warranty
Product Warranty Period (Mexico)	1-year limited warranty
Product Warranty Period (Puerto Rico)	1-year limited warranty

1000 Eaton Boulevard
 Cleveland, OH 44122
 United States
<https://tripplite.eaton.com>

© 2024 Eaton. All Rights Reserved.
 Eaton is a registered trademark. All other trademarks
 are the property of their respective owners.