



Powering Business Worldwide

## 6-ft. SCSI Ultra2/U160/U320 LVD Cable (Offset-VHDCI M/M with thumbscrews)

MODEL NUMBER: **S456-006**



### Highlights

- Premium double-shielded cable
- Meets the most current SCSI specifications for high-speed devices

### System Requirements

- Any external SCSI device or host controller card requiring VHDCI68M/M interface

### Package Includes

- 6-ft. SCSI U320/U160 LVD/SE cable, offset VHDCI68M/M w/thumbscrews

### Description

Moving your network into the next phase of SCSI solutions? Look no further than Tripp Lite's brand of SCSI U320/U160 cables. Supports all legacy transfer rates including Ultra 320 . Multi-platform SCSI III external peripheral cable, offset VHDCI68M/M. This 6ft cable is designed to connect two SCSI III (fast and wide) devices together. "Offset" connector with small footprint on VHDCI allows up to 4 channels to be attached to a single host bus adapter card. Manufactured using double shielded 34 twisted pair high impedance cable. Constructed with low-capacitance, impedance matched, 28 AWG, stranded, tinned copper cable with insulated in polypropylene.

### Features

- Backwards compatibility with previous SCSI generations
- Supports all SCSI transfer rates through 320Mbps
- LVD/SE compliant
- Double shielded (foil and braid)
- 34 twisted pair conductors
- All Tripp Lite SCSI products, regardless of the SCSI generation, meet the latest specifications of ANSI
- Tripp Lite offers a complete line of internal and external solutions for SCSI/RAID and fibre channel ranging from the very latest Ultra 320 to legacy SCSI-1 and every combination in between

## Specifications

OVERVIEW	
UPC Code	037332115577
CONNECTIONS	
Side A - Connector 1	VHDCI68 (MALE)
Side B - Connector 1	VHDCI68 (MALE)

PHYSICAL	
Color	Black
Cable Length (ft.)	6
Cable Length (m)	1.83
Shipping Dimensions (hwd / in.)	12.20 x 9.80 x 0.50
Shipping Dimensions (hwd / cm)	30.99 x 24.89 x 1.27
Shipping Weight (lbs.)	0.50
Shipping Weight (kg)	0.23
WARRANTY & SUPPORT	
Product Warranty Period (Worldwide)	Lifetime limited warranty

1000 Eaton Boulevard  
Cleveland, OH 44122  
United States  
<https://tripplite.eaton.com>

© 2024 Eaton. All Rights Reserved.  
Eaton is a registered trademark. All other trademarks  
are the property of their respective owners.