



Powering Business Worldwide

## 21-inch Internal SCSI U2/160 SCSI-LVD/SE 2-Drive Ribbon Cable with Terminator (3xHD68 M)

MODEL NUMBER: **S052-21I**



### Highlights

- Cable includes Active T-Type LVD/SE terminator

### System Requirements

- Wide SCSI controller card
- Internal SCSI drives and devices with HD68 Pin interface

### Package Includes

- 21-in. internal U2/160SCSI-LVD/SE 3Conn HD68M 2 drive with active terminator

### Description

Introducing Tripp Lite's internal SCSI Ultra2/U160 2-drive LVD ribbon cable with an active U160 terminator. This 21 inch cable is used to connect up to 2 SCSI devices to a SCSI host controller card. The cable is UL rated and is made with twist and flat "branded" ribbon. Because the cable is backwards compatible, it will support SCSI 1,2 & 3 devices such as CD-ROMs and Hard Drives. All Tripp Lite SCSI products, regardless of the SCSI generation, meet the latest SCSI specifications of ANSI (American National Standards Institute). For 3-Drive connection, see S053-36I.

### Features

- Ribbon cable connects up to 2 internal SCSI drives/devices to your internal SCSI controller
- HD68 male connectors
- Cable includes active terminator (T-type) LVD/SE terminator with local chip (ART IDC type)
- UL rated twist and flat "branded" cable
- SCSI U160 cables include active terminators which compensate for impedance mismatches
- All Tripp Lite SCSI products, regardless of the SCSI generation, meet the latest specifications of ANSI
- Tripp Lite offers a complete line of internal and external solutions for SCSI/RAID and fibre channel ranging from the very latest Ultra 320 to legacy SCSI-1 and every combination in between

## Specifications

OVERVIEW	
UPC Code	037332116055
Drives Supported	2
Technology	Ribbon/Internal; SCSI
CONNECTIONS	
Side A - Connector 1	INTERNAL HD68 (MALE)

Side B - Connector 1	HD68 (MALE)
PHYSICAL	
Color	Gray
Cable Length (ft.)	1.75
Cable Length (m)	0.53
Cable Length (in.)	21
Shipping Dimensions (hwd / in.)	9.30 x 7.00 x 0.75
Shipping Dimensions (hwd / cm)	23.62 x 17.78 x 1.90
Shipping Weight (lbs.)	0.21
Shipping Weight (kg)	0.10
WARRANTY & SUPPORT	
Product Warranty Period (Worldwide)	Lifetime limited warranty

1000 Eaton Boulevard  
Cleveland, OH 44122  
United States  
<https://tripplite.eaton.com>

© 2024 Eaton. All Rights Reserved.  
Eaton is a registered trademark. All other trademarks  
are the property of their respective owners.