

# 6-ft. SCSI Ultra2/U160/U320 LVD Cable (Offset-VHDCI-M/HD68M)

MODEL NUMBER: \$454-006



### **Highlights**

- Premium double-shielded cable
- Meets the most current SCSI specifications for high-speed devices

# **System Requirements**

 Any external SCSI device or host controller card requiring VHDCI68 or HD68 interface

#### **Package Includes**

 6-ft. SCSI U320/U160 LVD/SE cable, offset VHDCl68M to HD68M

## **Description**

Moving your network into the next phase of SCSI solutions? Look no further than Tripp Lite's brand of SCSI U320/U160 cables. Supports all legacy transfer rates including Ultra 320. Multi-platform SCSI III external peripheral cable, offset VHDCI68M/HD68M. This 6ft cable is designed to connect two SCSI III (fast and wide) or SCSI II devices together. "Offset" connector with small footprint on VHDCI allows up to 4 channels to be attached to a single host bus adapter card. Manufactured using double shielded 34 twisted pair high impedance cable. Constructed with low-capacitance, impedance matched, 28 AWG, stranded, tinned copper cable with insulated in polypropylene.

#### **Features**

- Small connector footprint on VHDCI connector allows up to 4 channels to be attached to a single host bus adapter card (a regular VHDCI connector will block access to an adjacent connector)
- Backwards compatibility with previous SCSI generations
- Supports all SCSI transfer rates through 320Mbps
- LVD/SE compliant
- Double shielded (foil and braid)
- 34 twisted pair conductors
- All Tripp Lite SCSI products, regardless of the SCSI generation, meet the latest specifications of ANSI
- Tripp Lite offers a complete line of internal and external solutions for SCSI/RAID and fibre channel ranging from the very latest Ultra 320 to legacy SCSI-1 and every combination in between

# **Specifications**

OVERVIEW	
UPC Code	037332115591
CONNECTIONS	
Side A - Connector 1	VHDCI68 (MALE)



Side B - Connector 1	HD68 (MALE)	
PHYSICAL		
Color	Black	
Cable Length (ft.)	6	
Cable Length (m)	1.83	
Shipping Dimensions (hwd / in.)	12.20 x 9.80 x 1.00	
Shipping Dimensions (hwd / cm)	30.99 x 24.89 x 2.54	
Shipping Weight (lbs.)	0.50	
Shipping Weight (kg)	0.23	
WARRANTY & SUPPORT		
Product Warranty Period (Worldwide)	Lifetime limited warranty	

1000 Eaton Boulevard Cleveland, OH 44122 United States https://tripplite.eaton.com © 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark. All other trademarks are the property of their respective owners.