

SCSI/Fibre Channel - 10-ft. SCSI U320/U160 LVD/SE Cable, Offset VHDCI68M to HD68M

MODEL NUMBER: **\$454-010**



Description

Moving your network into the next phase of SCSI solutions? Look no further than Tripp Lite's brand of SCSI U320/U160 cables. Supports all legacy transfer rates including Ultra 320 . Multi-platform SCSI III external peripheral cable, offset VHDCI68M/HD68M. This 10ft cable is designed to connect two SCSI III (fast and wide) or SCSI II devices together. "Offset" connector with small footprint on VHDCI allows up to 4 channels to be attached to a single host bus adapter card. Manufactured using double shielded 34 twisted pair high impedance cable. Constructed with low-capacitance, impedance matched, 28 AWG, stranded, tinned copper cable with insulated in polypropylene. Tripp Lite warrants this product to be free from defects in materials and workmanship for life.

Features

- Small connector footprint on VHDCI connector allows up to 4 channels to be attached to a single host bus adapter card (a regular VHDCI connector will block access to an adjacent connector)
- Backwards compatibility with previous SCSI generations
- Supports all SCSI transfer rates through 320Mbps
- LVD/SE compliant
- Double shielded (foil and braid)
- 34 twisted pair conductors
- All Tripp Lite SCSI products, regardless of the SCSI generation, meet the latest specifications of ANSI
- Tripp Lite offers a complete line of internal and external solutions for SCSI/RAID and fibre channel ranging from the very latest Ultra 320 to legacy SCSI-1 and every combination in between
- Tripp Lite warrants this product to be free from defects in materials and workmanship for life

Specifications

OVERVIEW UPC Code 037332121325 CONNECTIONS

Highlights

- Premium double-shielded cable
- Meets the most current SCSI specifications for high-speed devices

System Requirements

 Any external SCSI device or host controller card requiring VHDCI68 or HD68 interface

Package Includes

 10-ft. SCSI U320/U160 LVD/SE cable, offset VHDCI68M to HD68M



Side A - Connector 1	VHDCI68 (MALE)
Side B - Connector 1	HD68 (MALE)
PHYSICAL	
Cable Length (ft.)	10
Cable Length (m)	3.05
Shipping Dimensions (hwd / in.)	14.00 x 13.00 x 2.00
Shipping Dimensions (hwd / cm)	35.56 x 33.02 x 5.08
Shipping Weight (lbs.)	1.28
Shipping Weight (kg)	0.58
WARRANTY & SUPPORT	
Product Warranty Period (Worldwide)	Lifetime limited warranty

1000 Eaton Boulevard Cleveland, OH 44122 United States https://tripplite.eaton.com © 2024 Eaton. All Rights Reserved. Eaton is a registered trademark. All other trademarks are the property of their respective owners.