



SmartRack Pass-Through Side Panel with Key-Locking Latches for 42U Server Rack Cabinet, 2 Panels

MODEL NUMBER: SR42SIDEPT





Highlights

- Pre-installed latches lock securely with included keys to protect equipment from theft
- Brushed slots reduce dust ingress and allow easy cable routing in and out of the rack
- Made from heavy-duty steel engineered to stand up to busy IT environments
- Designed for use with 42 in. (1050 mm) depth, 42U rack enclosures
- Fits models based on the SR42UB frame design, including SR42UBEXP and SR42UBWD

Package Includes

- (2) Side panels with locking latches
- (2) Keys

Locking pass-through steel panels attach to the sides of your SR42UB-based server rack enclosure.

Features

Steel Pass-Through Side Panels for Installation on Your 42U Rack Cabinet

The SmartRack® SR42SIDEPT side panels feature pre-installed key-locking latches for securing your rack equipment against tampering and theft. Designed for standard-depth SR42UB rack frame, this panel can also be added to the side of an expansion cabinet (SR42UBEXP) when application needs have changed or onto a wide cabinet (SR42UBWD) as the depth remains the same. They can also be used as replacements for existing side panels.

Convert an Expansion Cabinet into a Cabinet with Side Panels

When needs change and you want to separate your expansion rack cabinets (such as SR42UBEXP), add four** SR42SIDEPT heavy-duty steel panels to the sides of them to convert the racks into standard cabinets with additional cable management functionality. **Note**: This package includes two (2) singular panels. You will need to purchase four SR42SIDEPT panels total to completely populate an expandable rack.

Specifications

OVERVIEW		
UPC Code	037332179128	
Accessory Type	Side Panel	
Accessory Class	Rack Accessories	
PHYSICAL		
Shipping Dimensions (hwd / in.)	36.00 x 4.00 x 41.50	
Shipping Dimensions (hwd / cm)	91.44 x 10.16 x 105.41	
Shipping Weight (lbs.)	43.00	





Shipping Weight (kg)	19.50	
Unit Dimensions (hwd / in.)	0.000 x 0.000 x 0.000	
Unit Dimensions (hwd / cm)	96.52 x 82.55 x 1.91	
Unit Weight (lbs.)	19.5	
Unit Weight (kg)	8.85	
STANDARDS & COMPLIANCE		
Product Compliance	RoHS	
WARRANTY & SUPPORT		
Product Warranty Period (Worldwide)	5-year limited warranty	

1000 Eaton Boulevard Cleveland, OH 44122 United States https://tripplite.eaton.com © 2024 Eaton. All Rights Reserved. Eaton is a registered trademark. All other trademarks are the property of their respective owners.