


## SmartRack 10-ft. x 1-ft. (3 m x 0.3 m) Cable Ladder, 2 sections - SRCABLETRAY/SRLADDERATTACH needed

MODEL NUMBER: SRCABLELADDER



### Description

SmartRack® SRCABLELADDER helps eliminate cable stress by organizing cables outside the Enclosure or Open Frame Rack. The cable ladder is 12 inches wide and 10 feet (3.1 meters) high. It ships in two convenient five-foot (1.5-meter) sections for easy shipping, storage and assembly. The SRCABLELADDER can be installed parallel or perpendicular to an enclosure. A grounding stud is provided to allow tie-in to the enclosure and facility ground. Toolless assembly and mounting on the SmartRack enclosure's top panel allows the cables to be safely routed overhead but must be connected to SRCABLETRAY. For Open Frame Rack installation, the SRLADDERATTACH is needed.

### Features

- SmartRack SRCABLELADDER helps eliminate cable stress by organizing cables outside of the SmartRack Enclosure or Open Frame Rack
- Safely routes cables overhead to and from enclosures
- The cable ladder is 12" wide and 10-ft. (3.05 m) high
- Ships in two convenient 5-ft. (1.52 m) sections for easy shipping, storage and assembly
- Can be installed parallel or perpendicular to an enclosure
- A grounding stud is provided to allow tie-in to the enclosure and facility ground

## Specifications

OVERVIEW	
UPC Code	037332143198
Accessory Type	Cable Management Accessories
PHYSICAL	
Color	Black

### Highlights

- Safely routes cables to eliminate cable stress
- Can be installed parallel or perpendicular to an enclosure
- Cable ladder is 12" wide
- Ships in two convenient 5-ft. (1.52 m) sections for easy shipping, storage and assembly
- Toolless assembly and mounting to enclosures
- Organizes cables outside of SmartRack enclosure or Open Frame Rack
- Grounding stud provided to allow tie-in to the enclosure and facility ground
- Must be connected to SRCABLETRAY when used with Enclosures or SRLADDERATTACH for Open Rack installations

### Package Includes

- SRCABLELADDER
- Mounting hardware
- Owner's manual



Powering Business Worldwide



Shipping Dimensions (hwd / in.)	3.20 x 12.80 x 61.00
Shipping Dimensions (hwd / cm)	8.13 x 32.51 x 154.94
Shipping Weight (lbs.)	13.00
Shipping Weight (kg)	5.90
Unit Dimensions (hwd / in.)	1.500 x 12.000 x 118.000
Unit Dimensions (hwd / cm)	3.81 x 30.48 x 299.72
Unit Weight (lbs.)	18
Unit Weight (kg)	8.16
FEATURES & SPECIFICATIONS	
IP68 Rated	No
IP20 Rated	No
STANDARDS & COMPLIANCE	
Product Compliance	RoHS; EIA/ECA-310-E
WARRANTY & SUPPORT	
Product Warranty Period (Worldwide)	5-year limited warranty

1000 Eaton Boulevard  
Cleveland, OH 44122  
United States  
<https://tripplite.eaton.com>

© 2024 Eaton. All Rights Reserved.  
Eaton is a registered trademark. All other trademarks  
are the property of their respective owners.