

# SmartRack 6 ft. (1.83 m) Vertical Cable Manager - Flexible ring type & toolless mounting

MODEL NUMBER: SRCABLERINGVRT



### Highlights

- Vertical Cable Manager, 6-ft. (1.83 m)
- Helps eliminate cable stress
- Organizes cables in racks
- Toolless button mounts
- Cold rolled steel with black finish
- Vertical Cable manager is split into two 3-ft. (0.91 m) sections for various installation options

### Package Includes

- Vertical Cable Manager, 6-ft. (1.83 m)

### Description

SmartRack® SRCABLERINGVRT helps eliminate cable stress by organizing the cables within the SmartRack enclosure or open rack cabinet. The vertical cable manager (flexible ring type) is six feet (1.8 meters) high and split into two three-foot (0.9-meter) sections to allow for multiple installation options. SRCABLERINGVRT offers toolless button mounting.

### Features

- SmartRack SRCABLERINGVRT helps eliminate cable stress by organizing the cables within the SmartRack enclosure or open rack cabinet
- The vertical cable manager (flexible ring type) is 6-ft. (1.83 m) high and split into two 3-ft. (0.91 m) sections to allow for multiple installation options
- Toolless button mounting

## Specifications

OVERVIEW	
UPC Code	037332140692
Accessory Type	Cable Management Accessories
PHYSICAL	
Color	Black
Shipping Dimensions (hwd / in.)	4.92 x 35.63 x 2.16
Shipping Dimensions (hwd / cm)	12.50 x 90.50 x 5.49
Shipping Weight (lbs.)	4.40
Shipping Weight (kg)	2.00
Unit Dimensions (hwd / in.)	34.000 x 3.500 x 2.000



Powering Business Worldwide



Unit Dimensions (hwd / cm)	86.36 x 8.89 x 5.08 (per 3 foot unit)
Unit Weight (lbs.)	3.7
Unit Weight (kg)	1.68
Cable Manager Form Factor	Vertical
<b>FEATURES &amp; SPECIFICATIONS</b>	
IP68 Rated	No
IP20 Rated	No
<b>STANDARDS &amp; COMPLIANCE</b>	
Product Compliance	RoHS; EIA/ECA-310-E
<b>WARRANTY &amp; SUPPORT</b>	
Product Warranty Period (Worldwide)	5-year limited warranty

1000 Eaton Boulevard  
Cleveland, OH 44122  
United States  
<https://tripplite.eaton.com>

© 2024 Eaton. All Rights Reserved.  
Eaton is a registered trademark. All other trademarks  
are the property of their respective owners.