

# SmartRack Roof-Mounted Cable Trough - Provides cable routing and power/data cable segregation

MODEL NUMBER: SRCABLETRAY



## Description

SmartRack® SRCABLETRAY safely routes cables across the top of an enclosure. When cabinets are lined in a row, these trays create a dedicated path for cables helping to eliminate cable stress. The SRCABLETRAY organizes cables outside of the SmartRack enclosure. It offers toolless mounting to the top of the rack panel. A grounding stud is provided to allow tie-in to the enclosure and the facility ground.

## Features

- SmartRack SRCABLETRAY safely routes cables across the top of an enclosure
- When cabinets are lined in a row, these trays create a dedicated path for cables helping to eliminate cable stress
- The SRCABLETRAY organizes cables outside of the SmartRack enclosure
- It offers toolless mounting to the top of the rack panel and a grounding stud is provided to allow tie-in to the enclosure and the facility ground

## Highlights

- Safely routes cables across the top of an enclosure
- When cabinets are lined in a row, these trays create a dedicated path for cables
- Helps eliminate cable stress
- Organizes cables outside of SmartRack enclosure
- Toolless mounting on the SmartRack enclosure's top panel
- Grounding stud provided to allow tie-in to the enclosure and facility ground

## Package Includes

- SRCABLETRAY trough section (1)
- Support Sections (2)
- #8-32 x 1/4 Phillips Screws (8)
- M6 Lock Washers (4)
- M6 Hex Nuts (2)
- 24-inch Ground Cable (1)

## Specifications

OVERVIEW	
UPC Code	037332140784
Accessory Type	Cable Management Accessories
PHYSICAL	
Color	Black
Shipping Dimensions (hwd / in.)	4.80 x 12.30 x 21.80
Shipping Dimensions (hwd / cm)	12.19 x 31.24 x 55.37
Shipping Weight (lbs.)	10.10



Powering Business Worldwide



Shipping Weight (kg)	4.58
Unit Dimensions (hwd / in.)	4.600 x 12.320 x 21.140
Unit Dimensions (hwd / cm)	11.68 x 31.29 x 53.70
Unit Weight (lbs.)	9
Unit Weight (kg)	4.08
<b>FEATURES &amp; SPECIFICATIONS</b>	
IP68 Rated	No
IP20 Rated	No
<b>STANDARDS &amp; COMPLIANCE</b>	
Product Compliance	RoHS; EIA/ECA-310-E
<b>WARRANTY &amp; SUPPORT</b>	
Product Warranty Period (Worldwide)	5-year limited warranty

1000 Eaton Boulevard  
Cleveland, OH 44122  
United States  
<https://tripplite.eaton.com>

© 2024 Eaton. All Rights Reserved.  
Eaton is a registered trademark. All other trademarks  
are the property of their respective owners.