

# External Battery Frame for Extended Runtime for select SmartOnline 20kVA & 30kVA 3-Phase UPS Systems

MODEL NUMBER: **SUBF2030**



### Highlights

- External Battery Frame holds up to four SURBC2030 Internal Battery Packs (available separately from Tripp Lite) to extend runtime
- High current DC connector attaches to select Tripp Lite SmartOnline 20kVA and 30kVA 3-Phase UPS Systems
- Simple installation and hot-swappable battery replacement supported

### Package Includes

- SUBF2030 External Battery Frame
- Instruction and installation manual

### Description

SUBF2030 is an External Battery Frame for use with select Tripp Lite SmartOnline 20kVA and 30kVA UPS Systems (SU20K3/3, SU20K3/3XR5, SU30K3/3 and SU30K3/3XR5). External Battery Frame supports the installation of up to four SURBC2030 Internal Battery Packs (available separately from Tripp Lite). Modular DC connector enables daisy chaining of multiple SUBF2030 External Battery Frames for extended runtime.

### Features

- SUBF2030 External Battery Frame allows users to extend battery runtime for select Tripp Lite SmartOnline 20kVA and 30kVA 3-Phase UPS Systems
- Each SUBF2030 supports up to four SURBC2030 Internal Battery Packs (available separately from Tripp Lite)
- Simple internal battery connections make battery installation and replacement fast and simple
- Internal Battery Packs that are designed for the SUBF2030 are separately fused. This removes shorted Battery Packs from the DC bus and maintains output from remaining Battery Packs

## Specifications

OVERVIEW	
UPC Code	037332137548
Accessory Type	Battery Frame
INPUT	
Input Phase	3-Phase
BATTERY	



Powering Business Worldwide



DC System Voltage (VDC)	240
<b>PHYSICAL</b>	
External Battery Pack Form Factor	Tower
Shipping Dimensions (hwd / in.)	23.00 x 24.00 x 39.00
Shipping Dimensions (hwd / cm)	58.42 x 60.96 x 99.06
Shipping Weight (lbs.)	113.00
Shipping Weight (kg)	51.26
Unit Dimensions (hwd / in.)	17.500 x 19.500 x 31.700
Unit Dimensions (hwd / cm)	44.5 x 49.53 x 80.5
Unit Weight (lbs.)	71
Unit Weight (kg)	32.21
<b>WARRANTY &amp; SUPPORT</b>	
Product Warranty Period (Worldwide)	2-year limited warranty

1000 Eaton Boulevard  
Cleveland, OH 44122  
United States  
<https://tripplite.eaton.com>

© 2024 Eaton. All Rights Reserved.  
Eaton is a registered trademark. All other trademarks  
are the property of their respective owners.