



**Tripp Lite**  
1111 West 35th Street  
Chicago, IL 60609 USA  
Telephone: +(773) 869 1234  
E-mail: [saleshelp@tripplite.com](mailto:saleshelp@tripplite.com)

## Model #: TRAVELER3USB

### Travel-Size Surge Suppressor with USB Charging Ports for Cell Phones, Music Players, and PDAs



#### Highlights

- 3 AC power outlets
- 540 joule rating
- Concealable Power Cord
- 2-USB Charging Ports
- Includes Mini USB Cable
- \$25,000 Ultimate Lifetime Insurance (USA, Puerto Rico & Canada only)

#### Description

Tripp Lite's portable TRAVELER3USB surge suppressor offers complete surge suppression for laptops, electronic notepads, personal organizers and other portable electronic devices. Compact and portable, it neatly fits into laptop travel cases. Concealable cord allows for ease of storage without scratching expensive electronics. With the addition of 2 USB Charging Ports, the TRAVELER3USB allows Road Warriors the ability to charge cell phone, MP3 Players and other portable devices more easily. TRAVELER3USB offers 3 total outlets which can accommodate a transformer, 2 USB Charging Ports and a diagnostic LED to warn of wiring problems and suppressor damage. \$25,000 Ultimate Lifetime Insurance (USA & Canada Only).

PLUG/OUTLETS: Input: NEMA5-15P/Output: 3 NEMA5-15R

ELECTRICAL: 120V AC, 50/60Hz, 15A (Requires NEMA5-15R wall receptacle)

FORMAT: Corded mobile surge with 1 transformer access

SUPPRESSION: AC: 540 joules

- 540 joules AC surge suppression shields equipment from the strongest surges and line noise
- 3 AC outlets with room for 1 transformer plug without blocking outlets.
- 2 USB Charging Ports for Cell phones, MP3 Players and more
- Portable housing with concealable cord allow for ease of mobility and travel in briefcases
- Diagnostic LED confirm outlet surge suppression status
- Lifetime warranty with \$25,000 Ultimate Lifetime Insurance (USA & Canada Only)

#### Applications

- Ideal for use with laptops, electronic notepads, personal organizers and other portable electronic devices.

#### Package Includes

- TRAVELER3USB Surge Suppressor
- Mini USB Cable

#### Specifications

##### OVERVIEW

Intended Application	Home/Office, Travel
<b>SYSTEM OVERVIEW</b>	
Voltage compatibility	120 VAC
<b>OUTPUT</b>	
Output Watt Capacity (watts)	1800
Frequency compatibility	60 Hz
Output VA	15 amps
Outlet quantity / type	3 NEMA 5-15R AC Outlets
Transformer accommodation	Supports up to 1 large transformer plug accessory without covering remaining outlets
<b>INPUT</b>	
Recommended Electrical Service	120V (110-125V)
Input connection type	NEMA 5-15P
Input cord length (ft.)	1-ft.
<b>LEDS ALARMS &amp; SWITCHES</b>	
Diagnostic LEDs	Built-in LED confirm suppressor "protection present" (green) status
<b>SURGE / NOISE SUPPRESSION</b>	
AC suppression joule rating	540 joules
Protection modes	Includes Line to Neutral (L-N), Neutral to Ground (N-G) and Line to Ground (L-G) line surge suppression
Clamping voltage (RMS)	150V
UL1499 let through rating	330V - UL Verified
<b>DATALINE SURGE SUPPRESSION</b>	
Telephone/DSL Protection	No
Cable (Coax) Protection	No
Network (Ethernet) Protection	No
<b>PHYSICAL</b>	
Shipping weight (lbs)	.66
Unit Dimensions (HWD/in)	4.75 x 3.5 x 1.5
Shipping Dimensions (HWD/in)	6.75 x 4.6 x 1.5
Unit weight (lbs)	.45
Material of construction	Plastic
<b>CONNECTIONS</b>	
Ports	2 USB Charging Ports
<b>SPECIAL FEATURES</b>	

<b>Appearance</b>	Ultra-compact, portable suppressor with concealable power cord fits easily in carrying case for laptops and other portable electronics
<b>Right-Angle Plug</b>	Yes
<b>CERTIFICATIONS</b>	
<b>UL1449 1998 Rev. (AC Suppression)</b>	UL1449
<b>cUL / CSA (Canada)</b>	cUL
<b>WARRANTY</b>	
<b>Standard warranty period</b>	Lifetime
<b>Connected equipment insurance (USA, Canada, Puerto Rico)</b>	\$25,000 Ultimate Lifetime Insurance

More information, including related products, owner's manuals, and additional technical specifications, can be found online at [www.tripplite.com/en/products/model.cfm?txtModelID=4315](http://www.tripplite.com/en/products/model.cfm?txtModelID=4315).