



**Tripp Lite**  
1111 West 35th Street  
Chicago, IL 60609 USA  
Telephone: +(773) 869 1234  
E-mail: [saleshelp@tripplite.com](mailto:saleshelp@tripplite.com)

## Model #: U232-006

### 6-ft. USB2.0 Hi-speed File Transfer Cable (USB A/A)

#### Highlights

- Ideal for transferring files between a notebook and desktop
- USB 2.0 hi-speed compliant
- Plug-n-play for easy installation and use



#### Description

Tripp Lite's U232-006, USB 2.0 hi-speed file transfer cable, provides a simple way to connect two computers via their USB ports, in order to quickly and easily exchange files. The cable provides true plug-n-play capability, while transferring files at much greater speeds than USB 1.1 file transfer products. The included PCLinQ2 application program provides a drag-n-drop, user friendly interface to transfer files. You simply plug in the U232-006 cable and install the application software into your PC(s). Tripp Lite 1-Year Limited Warranty.

#### Applications

- File sharing between two non-networked computers

#### System Requirements

- IBM PC Pentium 133 or higher compatible system
- Available USB 2.0 port (up to 480Mbps) or available USB 1.1 port (up to 12Mbps)
- CD-ROM Drive
- Windows 98/ME/2000/XP



#### Package Includes

- 1 U232-006 USB 2.0 File Transfer Cable
- 1 Users Manual
- Driver Software on CD

#### Features

- USB 2.0 hi-speed compliant
- Single cable solution for files transfer
- Printer and storage sharing between two computers
- USB networking - Ethernet emulation
- Drag-n-drop user-friendly interface
- No external power needed
- Supports Windows 98/ME/2000/XP

#### Specifications

OVERVIEW	
Intended Application	Connecting Peripherals
INPUT	
Cable Length (ft.)	6
PHYSICAL	
Color	Silver
Style	USB
CONNECTIONS	
Connector A	 USB A (MALE)
Connector B	 USB A (MALE)
Number of Connectors	2

## Related Items

### Optional Products

Product Type	Related Model	Description	Qty.
USB Cables & Adapters	<a href="#">U022-006</a>	6-ft. USB2.0 A/B Gold Device Cable (A Male to B Male)	1
USB Cables & Adapters	<a href="#">U022-010</a>	10-ft. USB2.0 A/B Gold Device Cable (A Male to B Male)	1
USB Cables & Adapters	<a href="#">U022-015</a>	15-ft. USB2.0 A/B Gold Device Cable (A Male to B Male)	1
USB Cables & Adapters	<a href="#">U024-006</a>	6-ft. USB A/A Gold Extension Cable for USB2.0 Cable (USB-A M/F)	1
USB Cables & Adapters	<a href="#">U024-010</a>	10-ft. USB A/A Gold Extension Cable for USB2.0 Cable (USB-A M/F)	1
USB Cables & Adapters	<a href="#">U026-016</a>	16-ft. USB2.0 A/A Active Extension Cable (USB-A M/F)	1
USB Cables & Adapters	<a href="#">U209-000-R</a>	USB to Serial Adapter (USB-A Male to DB9M)	1
USB Cables & Adapters	<a href="#">U222-004-R</a>	4-Port USB2.0 Ultra-Mini Hub	1

More information, including related products, owner's manuals, and additional technical specifications, can be found online at [www.tripplite.com/en/products/model.cfm?txtModelID=2954](http://www.tripplite.com/en/products/model.cfm?txtModelID=2954).

Copyright © 2011 Tripp Lite. All rights reserved. All trademarks are the sole property of their respective owners. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Photos may differ slightly from final products.