



Tripp Lite
1111 West 35th Street
Chicago, IL 60609 USA
Telephone: +(773) 869 1234
E-mail: saleshelp@tripplite.com

Model #: U239-000-R

USB2.0 to SATA Hard Drive Dock - Docking Station

Highlights

- Plug in 2.5" or 3.5" SATA drives for instant external storage
- Plug and Play - no tools, software or configuration required
- High Speed USB 2.0 480Mbps transfer speeds



Description

Tripp Lite's USB 2.0/SATA Hard Drive Dock gives you a quick and easy way to set up an external hard drive storage system. Plug the docking station into an available USB port on your computer or hub and pop in a 2.5" or 3.5" SATA drive for an instant external storage device. Far easier than installing the hard drive internally or in a caddy, the USB/SATA Dock is easy to use, convenient and practical. Compatible with Windows 2000/XP/Vista, and MAC with MAC OS X 10.3 or above. Includes 100-240V AC Adapter and 4-ft. USB 2.0 A-B cable. No disk drives are included with this unit. Tripp Lite Limited One Year Warranty.

Applications

- Formatting hard drives, File transfers, or External Storage

System Requirements

- Intel compatible PC w/USB Port (USB 2.0 recommended) and Windows 2000/XP/Vista
- Macintosh with USB 2.0 port and MAC OS X 10.3 (or above)

Package Includes

- U239-000-R USB 2.0/SATA Hard Drive Dock 4-ft. USB 2.0 A/B Cable
- Universal AC Adapter (100-240 VAC)
- Warranty Information

Features

- Instant SATA external storage for 2.5" and 3.5" drives
- Plug-n-Play (no software or configuring needed)
- USB 2.0 hi-speed transfer rates @ 480Mbps
- Windows 2000/XP/Vista, MAC OS X 10.3 (or above) compatible
- Heavy-weighted base for stability
- Push button ejection of drives
- Tripp Lite One Year Limited Warranty

Specifications

OVERVIEW

AC Adapter

100-240 VAC

PHYSICAL

Color

Black

Related Items**Optional Products**

Product Type	Related Model	Description	Qty.
USB Hubs/Accessories	U256-025	USB 2.0 External 2.5" IDE Hard Drive Enclosure	1

More information, including related products, owner's manuals, and additional technical specifications, can be found online at www.tripplite.com/en/products/model.cfm?txtModelID=3769.

Copyright © 2011 Tripp Lite. All rights reserved. All trademarks are the sole property of their respective owners. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Photos may differ slightly from final products.