



Tripp Lite
1111 West 35th Street
Chicago, IL 60609 USA
Telephone: +(773) 869 1234
E-mail: saleshelp@tripplite.com

Model #: U222-007-R

7-Port USB2.0 Hub



Highlights

- Connect up to 7 USB Peripherals
- Hi-Speed 480Mbps data transfer
- Backward compatible to USB 1.1
- Over-current protection safeguards connected equipment from overvoltages
- Included base stand for upright positioning

Description

Tripp Lites ultra small 7-port USB 2.0 hub is the most versatile and powerful hub on the market. This USB 2.0 certified hub allows you to connect up to seven USB devices to a single USB port on a Notebook/PC/MAC. This unit has been certified by the USB-IF to support Hi-Speed data transmission rates up to 480Mbps. Perfect for both the mobile and desktop user. While the hub will function perfectly in virtually all cases without needing external power, a compact, multi-voltage AC adapter (110/220V) has been provided for the rare circumstance when connecting a power hungry device. This USB 2.0 device is backwards compatible so that it will function with both USB 2.0 devices as well as USB 1.1 peripherals. Over-current protection safeguards connected equipment from overvoltages. Includes stand for upright positioning. Tripp Lite offers a lifetime replacement warranty on all cable products.

Applications

- Notebook and desktop computers

System Requirements

- Windows® 98/SE/2000/ME/XP/Vista/MAC
- USB port

Package Includes



- U222-007-R USB 2.0 Certified 7-Port Mini Hub
- Compact 110/220V AC power adapter, with NEMA 1-15P plug
- 4 ft. extension cable
- Instructions

Features

- USB2.0 Certified Hub
- Supports all data transfer rates up to 480Mbps
- Features 7-ports to increase the number of available USB ports on a computer
- Compact design is ideal for use with a laptop/notebook computer
- Does not require external power, software, or complicated set-up procedures
- Plug-and-play/hot-swappable allows you to add or remove a device at any time
- Per-port overcurrent protection (500mA max. as per the USB specified)

- Bus-powered or self-powered
- Compact, multi-voltage power supply (110/220V) provided
- Compatible with Windows 98, Windows 98 SE, Windows 2000, Windows ME, Windows XP, Vista and Mac OS 8.6 or higher
- Tripp Lite warrants this product to be free from defects in materials and workmanship for life

Specifications

OVERVIEW	
AC Adapter	Input: 100-240VAC, 50/60Hz, 0.5A 30VA Output per port: +5V, 500mA
PHYSICAL	
Color	Black/White
CONNECTIONS	
Connector A	 USB A (FEMALE)
Connector B	 USB B (FEMALE)
Number of Connectors	8
Ports	7 (USB-A)
CERTIFICATIONS	
Approvals	USB 2.0 Certified, FCC and CE

Related Items

Optional Products

Product Type	Related Model	Description	Qty.
USB Cables & Adapters	U022-006	6-ft. USB2.0 A/B Gold Device Cable (A Male to B Male)	-
USB Cables & Adapters	U022-010	10-ft. USB2.0 A/B Gold Device Cable (A Male to B Male)	-
USB Cables & Adapters	U022-015	15-ft. USB2.0 A/B Gold Device Cable (A Male to B Male)	-
USB Cables & Adapters	U024-006	6-ft. USB A/A Gold Extension Cable for USB2.0 Cable (USB-A M/F)	-
USB Cables & Adapters	U024-010	10-ft. USB A/A Gold Extension Cable for USB2.0 Cable (USB-A M/F)	-
USB Cables & Adapters	U209-000-R	USB to Serial Adapter (USB-A Male to DB9M)	-

More information, including related products, owner's manuals, and additional technical specifications, can be found online at www.tripplite.com/en/products/model.cfm?txtModelID=3167.