



**Tripp Lite**  
1111 West 35th Street  
Chicago, IL 60609 USA  
Telephone: +(773) 869 1234  
E-mail: [saleshelp@tripplite.com](mailto:saleshelp@tripplite.com)

## Model #: UPSWM

### Wallmount Bracket and installation accessories (4 washers, 4 screws, 1 Velcro safety strap)



#### Highlights

- Affixes compatible UPS systems to the wall
- Includes bracket, hardware and velcro strap

#### Description

Tripp Lite's Wallmount Bracket enables compatible UPS systems to attach to any wall or sturdy, vertical surface.

#### Applications

- Ideal for anyone looking to hang their UPS system or compatible battery pack from a wall

#### Package Includes

- Wallmount Bracket and installation accessories (4 washers, 4 screws, 1 Velcro safety strap)
- Mounting instructions

#### Features

- Allows compatible UPS systems or battery packs to hang from wall or other sturdy surface
- Compatible with Tripp Lite UPS systems BCPERSONAL300, BCPERSONAL450, BCPRO600, BCPRO850, BCPRO1050, BCPRO1400, INTERNETOFFICE500, INTERNETOFFICE700, OMNISMART300, OMNISMART350HG, OMNISMART450HG, OMNISMART500, OMNISMART700, OMNISMART700HG, OMNISMART1050, ONMISMART1400, OMNISMART1400HG, OMNIVS800, OMNIVS1000, OMNIVS1500XL, SMART550USB, SMART700, SMART700SER, SMART700HG, SMART750USB, SMART1050, SMART1200XLHG, SMART1500, SMART1500XL, TE600, TE1200 and other UPS systems that specify compatibility with this bracket
- Compatible with Tripp Lite Battery pack BP24V14

#### Specifications

OVERVIEW	
Model Type	Mounting Brackets
PHYSICAL	
Shipping weight (lbs)	7.0
Shipping weight (kg)	3.18
Unit Dimensions (HWD/in)	12.75 x 9.1 x 13.5

<b>Unit Dimensions (HWD/cm)</b>	32.38 x 23.1 x 34.3
<b>Shipping Dimensions (HWD/in)</b>	13.0 x 9.6 x 14.0
<b>Shipping Dimensions (HWD/cm)</b>	32.0 x 24.4 x 35.6
<b>Unit weight (lbs)</b>	6.8
<b>Unit weight (kg)</b>	3.0
<b>Material of construction</b>	Metal
<b>WARRANTY</b>	
<b>Product Warranty Period (U.S., Canada &amp; Puerto Rico)</b>	Not applicable

More information, including related products, owner's manuals, and additional technical specifications, can be found online at [www.tripplite.com/en/products/model.cfm?txtModelID=2671](http://www.tripplite.com/en/products/model.cfm?txtModelID=2671).

Copyright © 2012 Tripp Lite. All rights reserved. All trademarks are the sole property of their respective owners. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Photos may differ slightly from final products.