



**Tripp Lite**  
1111 West 35th Street  
Chicago, IL 60609 USA  
Telephone: +(773) 869 1234  
E-mail: [saleshelp@tripplite.com](mailto:saleshelp@tripplite.com)

## Model #: USA-49WG

### Keyspan High-Speed 4-Port Serial to USB Adapter

#### Highlights

- Zero configuration, Plug-and-Play operation
- Quickly connect and disconnect adapter without powering down
- Adds four RS-232 DB9 serial ports
- Detachable 6-ft. USB cable included
- No external power adapter required
- Mac OS and Windows-compatible



#### Description

Our USB 4-Port Serial Adapter allows 4 serial devices to be connected to a single USB port. It provides a simple way to add serial ports to a PC without the hassle of installing a serial card, turning off the PC, or configuring IRQs.

#### Applications

This adapter is ideal for industrial and enterprise markets where there is a need to connect serial device to a PC for process control, data collection, or point of sale applications. It is also ideal for connecting modems, fax modems, or terminals to a server.

#### System Requirements

##### Windows:

- An available USB port
- Compatible with Windows 98, 98 SE, Me, 2000, XP 32- and 64-bit, 2003 Server 32- and 64-bit, Vista 32- and 64-bit, and 7 32- and 64-bit

##### Macintosh:

- An available USB port
- Compatible with Mac OS 8.6 through 9.x, Mac OS X 10.2.8 through 10.5.x (both 32- and 64-bit), and Mac OS X 10.6.x (32-bit and 64-bit)

For use with all RS-232 serial devices including modems, GPS devices, cell phones, hand held scanners, networking equipment (console port), graphics tablets, point of sale devices, touch screens, UPS devices, medical and scientific instruments, industrial process control devices, building automation instrumentation and other serial devices.



#### Package Includes

- USA-49WG 4-Port USB Serial Adapter
- 6 ft. USB device cable
- CD with driver software and user guide

## Features

- High Speed: Supports 460 Kbps - four times the speed of a built-in serial port
- Detachable Cable: Use adapter with any USB cable (up to 5 meters long)
- LEDs: Show adapter status and data activity
- Plug & Play: Appear as standard COM ports
- Bus Powered: No external power adapter required
- Analytic Tools: Includes Windows line monitor and data trace software
- Field Upgrade: Easy to update over time with free software downloads
- Easy Expansion: Supports use of multiple adapters on one PC

## Specifications

PRODUCT OVERVIEW	
Product Overview	Keyspan-by-Tripp Lite 4-Port USB Serial Adapter
PHYSICAL	
Unit Dimensions (HWD/in)	1.8 x 6 x 3
Unit weight (lbs)	0.35
Color	Black
CONNECTIONS	
Connector A	 USB A (MALE)
Connector B	 (X4) DB9 (MALE)
WARRANTY	
Product Warranty Period (U.S., Canada & Puerto Rico)	2-year limited warranty

## Related Items

### Optional Products

Product Type	Related Model	Description	Qty.
Computer Cables	<a href="#">P520-006</a>	6-ft. RS-232 Serial Extension Cable (DB9 M/F)	1
USB Cables & Adapters	<a href="#">U022-006</a>	6-ft. USB2.0 A/B Gold Device Cable (A Male to B Male)	1
USB Cables & Adapters	<a href="#">U022-010</a>	10-ft. USB2.0 A/B Gold Device Cable (A Male to B Male)	1
USB Cables & Adapters	<a href="#">U022-015</a>	15-ft. USB2.0 A/B Gold Device Cable (A Male to B Male)	1
USB Cables & Adapters	<a href="#">U024-006</a>	6-ft. USB A/A Gold Extension Cable for USB2.0 Cable (USB-A M/F)	1
USB Cables & Adapters	<a href="#">U024-010</a>	10-ft. USB A/A Gold Extension Cable for USB2.0 Cable (USB-A M/F)	1
USB Cables & Adapters	<a href="#">U026-016</a>	16-ft. USB2.0 A/A Active Extension Cable (USB-A M/F)	1
USB Cables & Adapters	<a href="#">U042-036</a>	36-ft. High-Speed USB2.0 A/B Active Device Cable (A Male to B Male)	1

USB Cables & Adapters	<a href="#">U209-000-R</a>	USB to Serial Adapter (USB-A Male to DB9M)	1
USB Cables & Adapters	<a href="#">UPR-112G</a>	Mini-Port Replicator Keyspan by Tripp Lite	1
USB Cables & Adapters	<a href="#">USA-19HS</a>	High-Speed USB Serial Adapter Keyspan by Tripp Lite	1
USB Cables & Adapters	<a href="#">USA-28XG</a>	USB Twin Serial Adapter for Macs Keyspan by Tripp Lite	1

More information, including related products, owner's manuals, and additional technical specifications, can be found online at [www.tripplite.com/en/products/model.cfm?txtModelID=3916](http://www.tripplite.com/en/products/model.cfm?txtModelID=3916).

---

Copyright © 2011 Tripp Lite. All rights reserved. All trademarks are the sole property of their respective owners. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Photos may differ slightly from final products.