



**Tripp Lite**  
1111 West 35th Street  
Chicago, IL 60609 USA  
Telephone: +(773) 869 1234  
E-mail: [saleshelp@tripplite.com](mailto:saleshelp@tripplite.com)

## Model #: USA-19HS

### Keyspan High-Speed USB to Serial Adapter



#### Highlights

- Works with Windows and Mac OS (including v10.7 Lion)
- Connects RS-232/DB9 (male) to USB Type A (male)
- Detachable 3-ft. cable included
- No external power source required

#### Description

Looking for a way to connect a serial device to the USB port on your PC or Mac? Our USB High Speed Serial Adapter provides a simple and reliable solution. This adapter is broadly recommended by serial device manufacturers due to its dependability and "Best in Class" compatibility.

##### Applications

Connect older serial devices such as mice, keyboards, modems, GPS devices, barcode scanners, point-of-sale devices, lab equipment, programmable logic controllers (PLCs), digital signage and AV equipment to your new Mac or PC.

##### System Requirements

See "Downloads" tab for drivers.

##### Windows:

- An available USB port
- Compatible with Windows 98, 98 SE, Me, 2000, XP 32- and 64-bit, 2003 Server 32- and 64-bit, Vista 32- and 64-bit, and 7 32- and 64-bit

##### Macintosh:

- An available USB port
- Compatible with Mac OS 8.6 through 9.x, Mac OS X 10.2.8 through 10.5.x (both 32- and 64-bit), Mac OS X 10.6 (32-bit and 64-bit), and Mac OS X 10.7 Lion

For use with all RS-232 serial devices including modems, GPS devices, cell phones, hand held scanners, networking equipment (console port), graphics tablets, point of sale devices, touch screens, UPS devices, medical and scientific instruments, industrial process control devices, building automation instrumentation and other serial devices.

##### Package Includes



- USA-19HS USB High-Speed Serial Adapter
- 3 ft. USB device cable
- CD with driver software and user guide

#### Features

- Certified: Microsoft WHQL approved
- High Speed: Supports 230 Kbps - twice the speed of a built in serial port
- Detachable Cable: Use adapter with any USB cable (up to 5 meters long)
- LED: Shows adapter status and data activity
- Plug & Play: Appears as standard COM port
- Mobile: Easy to carry - weighs just 2 oz.
- Bus Powered: No external power adapter required

- Analytic Tools: Includes Windows line monitor and data trace software
- Field Upgrade: Easy to update over time with free software downloads
- Easy Expansion: Supports use of multiple adapters on one PC

## Specifications

PRODUCT OVERVIEW	
Product Overview	Keyspan-by-Tripp Lite USB High-Speed Serial Adapter
PHYSICAL	
Color	Black
CONNECTIONS	
Connector A	 DB9 (MALE)
Connector B	 USB A (MALE)
WARRANTY	
Product Warranty Period (U.S., Canada & Puerto Rico)	2-year limited warranty

## Related Items

### Optional Products

Product Type	Related Model	Description	Qty.
Computer Cables	<a href="#">P520-006</a>	6-ft. RS-232 Serial Extension Cable (DB9 M/F)	1
USB Cables & Adapters	<a href="#">U024-006</a>	6-ft. USB A/A Gold Extension Cable for USB2.0 Cable (USB-A M/F)	1
USB Cables & Adapters	<a href="#">U024-010</a>	10-ft. USB A/A Gold Extension Cable for USB2.0 Cable (USB-A M/F)	1
USB Cables & Adapters	<a href="#">U026-016</a>	16-ft. USB2.0 A/A Active Extension Cable (USB-A M/F)	1
USB Cables & Adapters	<a href="#">U209-000-R</a>	USB to Serial Adapter (USB-A Male to DB9M)	1
USB Cables & Adapters	<a href="#">USA-49WG</a>	4-Port USB Serial Adapter Keyspan by Tripp Lite	1

More information, including related products, owner's manuals, and additional technical specifications, can be found online at [www.tripplite.com/en/products/model.cfm?txtModelID=3914](http://www.tripplite.com/en/products/model.cfm?txtModelID=3914).

Copyright © 2011 Tripp Lite. All rights reserved. All trademarks are the sole property of their respective owners. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Photos may differ slightly from final products.