

Owner's Manual

Dual Flat-Panel Mobile Cart

Model: DMCS3545M



200x200 / 300x200
300x300 / 400x200
400x300 / 400x400



Este manual esta disponible en español en la página de Tripp Lite:
www.tripplite.com

Ce manuel est disponible en français sur le site Web de Tripp Lite :
www.tripplite.com

Русскоязычная версия настоящего руководства представлена на
веб-сайте компании Tripp Lite по адресу: www.tripplite.com

Dieses Handbuch ist in deutscher Sprache auf der Tripp Lite-Website
verfügbar: www.tripplite.com

PROTECT YOUR INVESTMENT!

Register your product for quicker service and ultimate peace of mind.
You could also win an ISOBAR6ULTRA surge protector—a \$100 value!
www.tripplite.com/warranty

TRIPP·LITE



Manufacturing
Excellence.

1111 W. 35th Street, Chicago, IL 60609 USA • www.tripplite.com/support

Copyright © 2019 Tripp Lite. All rights reserved.

NOTE: Read the entire instruction manual before you start assembly and installation.

WARNING

- **Do not begin the installation until you have read and understood the instructions and warnings contained in this manual. If you have questions regarding any of the instructions or warnings, please visit www.tripplite.com/support.**
- **This product was designed to be installed and utilized ONLY as specified in this manual. Improper installation of this product may cause damage or serious injury.**
- **This product should only be installed by someone of good mechanical ability, with basic building experience and a full understanding of this instruction manual.**
- **Make sure the unit can safely support the combined load of the equipment and all attached hardware and components.**
- **Always use an assistant or mechanical lifting equipment to safely lift and position equipment.**
- **This product is intended for indoor use only. Using this product outdoors could lead to product failure and/or personal injury.**

Warranty and Product Registration

5-Year Limited Warranty

Seller warrants this product, if used in accordance with all applicable instructions, to be free from original defects in material and workmanship for a period of 5 years from the date of initial purchase. If the product should prove defective in material or workmanship within that period, Seller will repair or replace the product, in its sole discretion.

THIS WARRANTY DOES NOT APPLY TO NORMAL WEAR OR TO DAMAGE RESULTING FROM ACCIDENT, MISUSE, ABUSE OR NEGLIGENCE. SELLER MAKES NO EXPRESS WARRANTIES OTHER THAN THE WARRANTY EXPRESSLY SET FORTH HEREIN. EXCEPT TO THE EXTENT PROHIBITED BY APPLICABLE LAW, ALL IMPLIED WARRANTIES, INCLUDING ALL WARRANTIES OF MERCHANTABILITY OR FITNESS, ARE LIMITED IN DURATION TO THE WARRANTY PERIOD SET FORTH ABOVE; AND THIS WARRANTY EXPRESSLY EXCLUDES ALL INCIDENTAL AND CONSEQUENTIAL DAMAGES. (Some states do not allow limitations on how long an implied warranty lasts, and some states do not allow the exclusion or limitation of incidental or consequential damages, so the above limitations or exclusions may not apply to you. This warranty gives you specific legal rights, and you may have other rights which vary from jurisdiction to jurisdiction).

WARNING: The individual user should take care to determine prior to use whether this device is suitable, adequate or safe for the use intended. Since individual applications are subject to great variation, the manufacturer makes no representation or warranty as to the suitability or fitness of these devices for any specific application.

PRODUCT REGISTRATION


Visit www.tripplite.com/warranty today to register your new Tripp Lite product. You'll be automatically entered into a drawing for a chance to win a FREE Tripp Lite product!*

* No purchase necessary. Void where prohibited. Some restrictions apply. See website for details.

Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Photos and illustrations may differ slightly from actual products.


Component Checklist

IMPORTANT: Ensure you have received all parts according to the component checklist prior to installing. If any parts are missing or faulty, visit www.tripplite.com/support for service.




Component Checklist

Package P




Package M




Assembly

1 Assemble the Base




Using M8x40 screws (**P-D**) and the 5 mm hex key (**P-N**), attach the right base to the middle base. Repeat this step for the left base.




Note: Lock the brakes on the casters to avoid any sudden movements during installation. Each caster can be adjusted independently for fine adjustments. Slightly turn each caster nut to lower or raise the base.

Assembly

2 Attach the Columns to the Base




Pull the pin outward and lift the inner column upward at the same time until the inner column is at the desired height. Release the pin to secure.



Assembly


3 Install the Crossbar



Using M6x14 screws (**P-H**), attach the crossbar to the columns.


Once the crossbar installation is completed, use the 5 mm hex key (**P-N**) to tighten the bottom screws on the base.

4 Install the Cable Covers




Assembly

5 Install the Universal Plate




Using M8x65 screws (**P-I**),
D8 washers (**P-L**) and butterfly
nuts (**P-B**), attach the universal
plate to the columns.




Assembly

6 Install the Adapter Brackets



6a Install the Adapter Brackets

For Flat-Back Screen



Note: Choose appropriate screws and washers according to the type of screen.






- Screw the adapter brackets onto the display.

⚠ Tighten all screws, but do not over-tighten.

Assembly

6b Install the Adapter Brackets

For Recessed-Back Screen or to Access A/V Inputs




Note: Choose appropriate screws, washers and spacers (if necessary) according to the type of screen.

- Screw the adapter brackets onto the display.

⚠ Tighten all screws, but do not over-tighten.

Assembly

7 Attach the Displays onto the Universal Plate




- Hang the displays onto the universal plate.
- Tighten the bottom screws to secure.


⚠ Make sure the displays are mounted correctly and the screws are tightened safely before releasing the displays.

Assembly

8 Install the Camera Shelf




Using M4x6 screws (**P-J**) and (**P-K**), attach the camera shelf to the connecting plate.




Using M6x25 screws (**P-F**) and D6 washers (**P-M**), attach the connecting plate to the universal plate.

Assembly

9 Install the DVD Shelf




Using M6x8 screws (**P-G**), attach the support bar to the columns at the desired position.



Using M6x25 screws (**P-F**), M6x8 screws (**P-H**) and butterfly nuts (**P-A**), attach the DVD shelf to the support bar.

Assembly




10 Cable Management



Route the cables through the cable covers.

Assembly

11 Adjustment



- Adjust the columns to the desired height before installing the display.
- If adjusting the column height after completing the display installation, first remove the DVD shelf, then adjust the columns to the desired height.

Maintenance

- Check that the bracket is secure and safe to use at regular intervals (at least every three months).
- Please visit www.triplite.com/support if you have any questions.



1111 W. 35th Street, Chicago, IL 60609 USA • www.triplite.com/support