


Owner's Manual

Pop-Out Video Wall

Model: DMVWSC4570XUL



For additional instructions on installing more than one video mount, visit www.tripplite.com.



200x200 / 300x200 / 300x300
400x200 / 400x300 / 400x400
600x400



Este manual esta disponible en español en la página de Tripp Lite: www.tripplite.com

Ce manuel est disponible en français sur le site Web de Tripp Lite : www.tripplite.com

Русскоязычная версия настоящего руководства представлена на веб-сайте компании Tripp Lite по адресу: www.tripplite.com

Dieses Handbuch ist in deutscher Sprache auf der Tripp Lite-Website verfügbar: www.tripplite.com

WARRANTY REGISTRATION

Register your product today and be automatically entered to win an ISOBAR surge protector in our monthly drawing!



www.tripplite.com/warranty



1111 W. 35th Street, Chicago, IL 60609 USA • www.tripplite.com/support

Copyright © 2019 Tripp Lite. All rights reserved.

NOTE: Read the entire instruction manual before you start assembly and installation.



WARNING

- **Do not begin the installation until you have read and understood the instructions and warnings contained in this manual. If you have any questions regarding any of the instructions or warnings, please visit www.tripplite.com/support**
- **This product was designed to be installed and utilized ONLY as specified in this manual. Improper installation of this product may cause damage or serious injury.**
- **This product should only be installed by someone of good mechanical ability, with basic building experience and a full understanding of this instruction manual.**
- **Make sure that the unit can safely support the combined load of the equipment and all attached hardware and components.**
- **Always use an assistant or mechanical lifting equipment to safely lift and position equipment.**
- **This product is intended for indoor use only. Using this product outdoors could lead to product failure and personal injury.**

Warranty and Product Registration

5-Year Limited Warranty

Seller warrants this product, if used in accordance with all applicable instructions, to be free from original defects in material and workmanship for a period of 5 years from the date of initial purchase. If the product should prove defective in material or workmanship within that period, Seller will repair or replace the product, in its sole discretion.

THIS WARRANTY DOES NOT APPLY TO NORMAL WEAR OR TO DAMAGE RESULTING FROM ACCIDENT, MISUSE, ABUSE OR NEGLIGENCE. SELLER MAKES NO EXPRESS WARRANTIES OTHER THAN THE WARRANTY EXPRESSLY SET FORTH HEREIN. EXCEPT TO THE EXTENT PROHIBITED BY APPLICABLE LAW, ALL IMPLIED WARRANTIES, INCLUDING ALL WARRANTIES OF MERCHANTABILITY OR FITNESS, ARE LIMITED IN DURATION TO THE WARRANTY PERIOD SET FORTH ABOVE; AND THIS WARRANTY EXPRESSLY EXCLUDES ALL INCIDENTAL AND CONSEQUENTIAL DAMAGES. (Some states do not allow limitations on how long an implied warranty lasts, and some states do not allow the exclusion or limitation of incidental or consequential damages, so the above limitations or exclusions may not apply to you. This warranty gives you specific legal rights, and you may have other rights which vary from jurisdiction to jurisdiction).

WARNING: The individual user should take care to determine prior to use whether this device is suitable, adequate or safe for the use intended. Since individual applications are subject to great variation, the manufacturer makes no representation or warranty as to the suitability or fitness of these devices for any specific application.

PRODUCT REGISTRATION


Visit www.tripplite.com/warranty today to register your new Tripp Lite product. You'll be automatically entered into a drawing for a chance to win a FREE Tripp Lite product!*

* No purchase necessary. Void where prohibited. Some restrictions apply. See website for details.


Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Photos and illustrations may differ slightly from actual products.

Component Checklist


IMPORTANT: Ensure that you have received all parts according to the component checklist prior to installing. If any parts are missing or faulty, visit www.tripplite.com/support for service.





Package M



Package W




Product Dimensions




Assembly

1 Attach Connecting Plates to Wall Plates






Using the M5x8 screws (E), attach the connecting plates to the wall plates.




Assembly

2a Mount on Wood Stud Wall




Mark the exact location of mounting holes



Drill pilot holes



Screw the wall plate onto the wall






Using the ST6.3x55 screws (**W-A**) and D6 washers (**W-C**), attach wall plate assembly to the wall.

WARNING

- Make sure that mounting screws are anchored into the center of the studs. Use of a stud finder is highly recommended.
- Installers are responsible to provide hardware for other types of mounting situations.
- Installers must verify that the supporting surface will safely support the combined load of the equipment and all attached hardware and components.

Assembly

2b Mount on Solid Brick or Concrete Block Wall




1
Mark the exact location of mounting holes

2
Drill pilot holes



Screw the wall plate onto the wall



Using the ST6.3x55 screws (W-A), D6 washers (W-C) and concrete anchors (W-B), attach wall plate assembly to the wall.

WARNING



- When installing wall mounts onto a concrete masonry unit (also known as a CMU or “cinder block”), verify that the actual concrete thickness is at least 35 mm (1-3/8”) in order to hold the concrete anchors. **DO NOT DRILL INTO MORTAR JOINTS!** Be sure to mount the assembled wall-mount plate with the included concrete anchors, washers and anchor bolts onto solid sections of the blocks.

The solid sections can generally be found 25 mm (1”) toward the middle of the block from either end. An electric drill on a slow setting is suggested to drill the hole rather than a hammer drill so as to avoid breaking out the back of the hole when entering a hollow section.

- Installers must verify that the supporting surface will safely support the combined load of the equipment and all attached hardware and components.

Assembly




3 Install the Pop-Out Adapter Brackets



For VESA 600x400 mounting patterns, the "D" and "C" positions are flipped.

Assembly

3a For Flat Back Screens






Note: Choose appropriate screws according to the type of screen.

- Firmly secure the adapter brackets onto the display using the screws and any other necessary hardware components included with the unit.

 **Do not over-tighten screws.**

Assembly

3b For Bump-Out Screen, Recessed Back Screen or to Access A/V Inputs




Note: Choose appropriate screws, washers and spacers (if necessary) according to the type of screen.

- Firmly secure the adapter brackets onto the display using the screws and any other necessary hardware components included with the unit.

 **Do not over-tighten screws.**

Assembly


4 Attach the Display onto the Wall Plate




Locking Plate

Turn the locking plates downward to fasten the wall plate. Tighten the screws to secure.

Use a padlock to prevent the display from tampering or theft.




5 Adjustment



For fast alignment, push the display to the left or right.


5a Micro Adjustment



For tilt adjustment.

For in/out micro adjustment.


For up/down micro adjustment.




Assembly

5b Tilt Adjustment

1







2




Assembly

5c Height Adjustment





Assembly

5d Depth Adjustment





Note: Only use the long end of the hex key when tightening the adjustment screws.


1




2



3




4



Assembly

6 Secure and Lock the Display

Use the plastic locks (F) to lock the display in place.



- Check that the bracket is secure and safe to use at regular intervals (at least every three months).
- Please visit www.tripplite.com/support if you have any questions.



1111 W. 35th Street, Chicago, IL 60609 USA • www.tripplite.com/support

LVW06-46T