

Owner's Manual

USB 3.0 to SATA / IDE Adapter with Built-in Cable

Model: U338-06N

Este manual esta disponible en español en la
página de Tripp Lite: tripplite.com/support

Ce manuel est disponible en français sur le site
Web de Tripp Lite : tripplite.com/support

Русскоязычная версия настоящего руководства
представлена на веб-сайте компании
Tripp Lite по адресу: tripplite.com/support

WARRANTY REGISTRATION

Register your product today and be automatically entered
to win an ISOBAR surge protector in our monthly drawing!

tripplite.com/warranty



1111 W. 35th Street, Chicago, IL 60609 USA
tripplite.com/support

Copyright © 2019 Tripp Lite. All rights reserved.

Package Contents

- U338-06N USB 3.0 to SATA / IDE Adapter
- 7-Pin SATA Data Cable
- 15-Pin SATA Power Cable
- 4-Pin Molex Power Cable
- Power Supply Adapter
- External Power Supply (Input: 100-240V, 50/60 Hz, 1.5A; Output: 12V 2A)
- Owner's Manual

Product Features

- Supports USB 3.0 SuperSpeed specification; backward compatible with USB 2.0 and 1.1
- Allows easy hard drive access without having to connect the drive internally
- Features SATA, 40-Pin and 44-Pin connectors for use with 2.5", 3.5" or 5.25" drives
- Compatible with Windows[®], Mac[®], and Linux[®] operating systems
- Plug-and-Play—no software or drivers required

System Requirements

- Computer with an available USB port; a USB 3.0 port is required to achieve USB 3.0 data transfer rates
- 2.5" / 3.5" / 5.25" SATA or IDE drive

Installation

Notes:

- *Hard drives are sensitive to static electricity and must be handled properly to prevent data loss. Always handle your hard drive with caution. Wear an anti-static strap (such as the Tripp Lite P999-000) when transporting it, or touch a grounded metal surface to discharge yourself of static electricity before picking up the drive.*
- *If your drive has not been formatted, you must format it using your computer's Disk Management utility before you can copy and access files.*
- *For all IDE devices, set the Jumper setting on the drive to Master Single drive mode. For Jumper settings, refer to your hard drive manufacturer's documentation.*
- *Before unplugging the adapter, make sure to properly eject the drive from your computer to avoid any potential data loss.*

Installation

1. Connect the external power supply to the included power supply adapter and plug it into an appropriate power source.

SATA Drive (For IDE drives, skip to Step 4)

2. Insert one end of the provided 7-Pin SATA data cable into the SATA port on the U338-06N and the other end to the SATA data port on the SATA hard drive.
3. Connect the included 15-Pin SATA Power Cable between the included power supply adapter and the SATA power port on the SATA hard drive. Go to Step 6.

IDE Drive

4. Align the IDE drive interface on the hard drive with the appropriate port on the U338-06N, then gently but firmly insert the IDE drive interface into it. Be sure the drive is firmly connected.
5. Connect the included 4-Pin Molex Power Cable between the included power supply adapter and the power port on the IDE hard drive.

Installation

6. Insert the built-in USB cable on the U338-06N into an available USB port on your computer. The LEDs on the U338-06N will illuminate if all devices are connected properly.

Note: *The two LEDs will illuminate solid blue to indicate the unit is powered on. They will blink when transmitting data.*

7. The hard drive should be automatically detected by your computer's operating system.

Warranty and Product Registration

3-Year Limited Warranty

TRIPP LITE warrants its products to be free from defects in materials and workmanship for a period of three (3) years from the date of initial purchase. TRIPP LITE's obligation under this warranty is limited to repairing or replacing (at its sole option) any such defective products. To obtain service under this warranty, you must obtain a Returned Material Authorization (RMA) number from TRIPP LITE or an authorized TRIPP LITE service center. Products must be returned to TRIPP LITE or an authorized TRIPP LITE service center with transportation charges prepaid and must be accompanied by a brief description of the problem encountered and proof of date and place of purchase. This warranty does not apply to equipment, which has been damaged by accident, negligence or misapplication or has been altered or modified in any way.

EXCEPT AS PROVIDED HEREIN, TRIPP LITE MAKES NO WARRANTIES, EXPRESS OR IMPLIED, INCLUDING WARRANTIES OF MERCHANTABILITY AND FITNESS FOR A PARTICULAR PURPOSE.

Some states do not permit limitation or exclusion of implied warranties; therefore, the aforesaid limitation(s) or exclusion(s) may not apply to the purchaser.

EXCEPT AS PROVIDED ABOVE, IN NO EVENT WILL TRIPP LITE BE LIABLE FOR DIRECT, INDIRECT, SPECIAL, INCIDENTAL OR CONSEQUENTIAL DAMAGES ARISING OUT OF THE USE OF THIS PRODUCT, EVEN IF ADVISED OF THE POSSIBILITY OF SUCH DAMAGE. Specifically, TRIPP LITE is not liable for any costs, such as lost profits or revenue, loss of equipment, loss of use of equipment, loss of software, loss of data, costs of substitutes, claims by third parties, or otherwise.

Warranty and Product Registration

PRODUCT REGISTRATION

Visit tripplite.com/warranty today to register your new Tripp Lite product. You'll be automatically entered into a drawing for a chance to win a FREE Tripp Lite product!*

* No purchase necessary. Void where prohibited. Some restrictions apply. See website for details.

FCC Notice, Class B

This device complies with part 15 of the FCC Rules. Operation is subject to the following two conditions: (1) This device may not cause harmful interference, and (2) this device must accept any interference received, including interference that may cause undesired operation.

Note: This equipment has been tested and found to comply with the limits for a Class B digital device, pursuant to part 15 of the FCC Rules. These limits are designed to provide reasonable protection against harmful interference in a residential installation. This equipment generates, uses and can radiate radio frequency energy and, if not installed and used in accordance with the instructions, may cause harmful interference to radio communications. However, there is no guarantee that interference will not occur in a particular installation. If this equipment does cause harmful interference to radio or television reception, which can be determined by turning the equipment off and on, the user is encouraged to try to correct the interference by one or more of the following measures:

- Reorient or relocate the receiving antenna.
- Increase the separation between the equipment and receiver.
- Connect the equipment into an outlet on a circuit different from that to which the receiver is connected.

Warranty and Product Registration

- Consult the dealer or an experienced radio/TV technician for help.

Any changes or modifications to this equipment not expressly approved by Tripp Lite could void the user's authority to operate this equipment.

WEEE Compliance Information for Tripp Lite Customers and Recyclers (European Union)



Under the Waste Electrical and Electronic Equipment (WEEE) Directive and implementing regulations, when customers buy new electrical and electronic equipment from Tripp Lite they are entitled to:

- Send old equipment for recycling on a one-for-one, like-for-like basis (this varies depending on the country)
- Send the new equipment back for recycling when this ultimately becomes waste

Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice.



Manufacturing
Excellence.

1111 W. 35th Street, Chicago, IL 60609 USA
triplite.com/support