

External 240V Tower Battery Pack for select Tripp Lite UPS Systems (BP240V400)

MODEL NUMBER: **BP240V400**



Highlights

- Extends runtime of compatible Tripp Lite UPS Systems using 240VDC configuration
- Internal DC disconnect
- 10 year design lifespan
- Hardwire installation
- Compliant with the Federal Trade Agreements Act (TAA) for GSA Schedule purchases

Description

Tripp Lite's BP240V400 External Battery Pack offers extended battery runtime when used in conjunction with compatible Tripp Lite UPS systems. Requires BP240EXTNDR15A to connect to UPS. Cabling for additional battery packs is contractor supplied.

COMPATIBLE UPS SYSTEMS: SU20K3/3, SU30K3/3 and other Tripp Lite UPS systems specifying the use of this battery pack

Features

- Offers extended-run UPS operation when used in conjunction with compatible Tripp Lite UPS systems
- Multiple battery packs can be daisy-chained through each other to the UPS for even longer extended run operation
- Internal DC disconnect
- 10 year design lifespan

Specifications

OVERVIEW	
UPC Code	037332185020
INPUT	
Input Phase	3-Phase
BATTERY	
Expandable Runtime	Yes
DC System Voltage (VDC)	240
UPS Connection	Requires BP240EXTNDR15A to connect to UPS



Powering Business Worldwide



PHYSICAL	
Material of Construction	Steel
External Battery Pack Form Factor	Tower
Shipping Dimensions (hwd / in.)	66.00 x 46.00 x 48.00
Shipping Dimensions (hwd / cm)	167.64 x 116.84 x 121.92
Shipping Weight (lbs.)	2200.00
Shipping Weight (kg)	997.90
Unit Dimensions (hwd / in.)	59.000 x 29.000 x 31.500
Unit Dimensions (hwd / cm)	149.9 x 73.7 x 80
Unit Weight (lbs.)	2020
Unit Weight (kg)	916.26
Unit Weight Details	Floor loading of 288 lbs per sq. ft. / 1410 kg per sq. meter
ENVIRONMENTAL	
Operating Temperature Range	32 to 104F; (0 to 40C)
Storage Temperature Range	5 to 104F; (-15 to 40C)
Relative Humidity	5 to 95% (non-condensing)
Operating Elevation	0 to 10,000
STANDARDS & COMPLIANCE	
Product Certifications	CSA (Canada); UL 1778
Product Compliance	RoHS; CE (Europe); UKCA
WARRANTY & SUPPORT	
Product Warranty Period (Worldwide)	1-year limited warranty

1000 Eaton Boulevard
 Cleveland, OH 44122
 United States
<https://tripplite.eaton.com>

© 2024 Eaton. All Rights Reserved.
 Eaton is a registered trademark. All other trademarks
 are the property of their respective owners.