


2.5-Inch SATA Hard Drive Mounting Kit for 3.5-Inch Drive Bay

MODEL NUMBER: P948-BRKT25



Highlights

- Easy transfer of data from 2.5 in. drive to your PC
- Supports all 2.5 in. SATA HDDs and SSDs
- Includes 22-pin data/power adapter cable
- Durable solid steel construction

Package Includes

- Bracket
- 22-pin data/power SATA adapter cable
- (8) Screws
- Owner's manual

Increases your desktop PC's performance by allowing you to mount a 2.5 in. SATA hard drive into an available 3.5 in. drive bay.

Description

The P948-BRKT25 2.5-Inch SATA Hard Drive Mounting Kit improves the performance of your desktop computer and allows you to add significant data storage. It allows you to mount a 2.5-inch SATA hard disk drive (HDD) or solid state drive (SSD) into an empty 3.5-inch drive bay on your PC. The solid steel bracket comes with a 22-pin data/power SATA adapter cable that attaches to the 2.5-inch drive's SATA port, the computer power supply's LP4 port and an available SATA data connector on the host motherboard. Screws for mounting the bracket are also included.

Features

Mounts a 2.5 in. SATA Drive Into a 3.5 in. Drive Bay

- Easy transfer of data from 2.5 in. drive to your PC
- Adds significant amount of data storage
- Durable solid steel construction
- Supports all 2.5 in. SATA HDDs and SSDs
- 22-pin data/power adapter cable and mounting hardware included

Specifications

OVERVIEW	
UPC Code	037332200501
Technology	SATA/eSATA
CONNECTIONS	
Side A - Connector 1	22 PIN SATA + POWER (FEMALE)
Side B - Connector 1	7 PIN SATA (MALE)



Powering Business Worldwide



Side B - Connector 2	LP4 (MALE)
PHYSICAL	
Color	Black
Shipping Dimensions (hwd / in.)	1.00 x 4.10 x 6.20
Shipping Dimensions (hwd / cm)	2.54 x 10.41 x 15.75
Shipping Weight (lbs.)	0.30
Shipping Weight (kg)	0.14
Unit Dimensions (hwd / in.)	0.000 x 0.000 x 0.000
Unit Dimensions (hwd / cm)	1.3 x 10.1 x 6.1
FEATURES & SPECIFICATIONS	
IP68 Rated	No
IP20 Rated	No
STANDARDS & COMPLIANCE	
Product Compliance	RoHS; REACH
WARRANTY & SUPPORT	
Product Warranty Period (Worldwide)	Lifetime limited warranty

1000 Eaton Boulevard
Cleveland, OH 44122
United States
<https://tripplite.eaton.com>

© 2024 Eaton. All Rights Reserved.
Eaton is a registered trademark. All other trademarks
are the property of their respective owners.