



Protect It! 230V Surge Protector with 8 Schuko Type F Outlets, German Plug, 2280 Joules, Tel/Coax Protection

MODEL NUMBER: TLP82NSATD



Highlights

- · 8 safety outlets
- 2 m cord
- Network protection
- 1 Line coax protection
- Protected/Grounded LED's
- 2280 joule rating

Package Includes

- TLP82NSATD surge suppressor
- 1.8 aerial cable and 2 aerial adapters
- 1.8 m gold coax cable
- 1.8 m network cable
- Instruction manual and warranty information

Description

Tripp Lite's Protect It!™ TLP82NSATD offers economical AC surge suppression for full protection of 220-250V home computers, printers, scanners, and desk lamps. The TLP82NSATD offers 8 Schuko type F outets and a 2 meter AC line cord. Internal safety covers protect against accidental contact with unused outlets.

Features

- Protect It!™ TLP82NSATD offers economical AC surge supression
- 2280 joules AC surge suppression shields equipment from surges and line noise
- 8 Schuko outlets protects computers and peripherals
- 2 m cord with German plug
- Lighted ON/OFF switch with circuit breaker
- Protected/Grounded LED's
- Network Protection
- Coax Protection
- Aerial Adapters
- Internal safety covers protect against accidental contact with unused outlets

Specifications

OVERVIEW		
UPC Code	037332145413	
INPUT		
Nominal Input Voltage(s) Supported	230V AC	





Recommended Electrical Service	230V (220-250V)	
Maximum Input Amps	10	
Voltage Compatibility (VAC)	220-250	
Input Plug Type	German	
Input Cord Length (ft.)	6	
Right-Angle Plug	Yes	
Input Cord Length (m)	1.83	
Integrated Cord Clip	No	
OUTPUT		
Output Receptacles	(8) Schuko Type F	
Circuit Breaker (amps)	10	
Transformer Accommodation	(5) Yes	
USER INTERFACE, ALERTS & CONTROLS		
Diagnostic LED(s)	Yes	
Diagnostic LED Details	Protected and Grounded	
SURGE / NOISE SUPPRESSION		
AC Suppression Joule Rating	2280	
Automatic Shut-Off	No	
DATALINE SURGE SUPPRESSION		
Cable (Coax) Protection	Yes	
Cable (Coax) Protection Details	1 line	
Network (Ethernet) Protection	Yes	
Network (Ethernet) Protection Details	1 line	
Telephone/DSL Protection	Yes	
PHYSICAL		
Color	Black	
Power Cord Color	Black	
Housing Color	Black	
Mounting Holes or Slots	No	
Receptacle Color	Black	
Shipping Dimensions (hwd / in.)	14.80 x 7.80 x 2.18	
Shipping Dimensions (hwd / cm)	37.59 x 19.81 x 5.54	





Shipping Weight (lbs.)	2.50	
Shipping Weight (kg)	1.13	
Unit Dimensions (hwd / in.)	12.440 x 4.610 x 1.930	
Unit Dimensions (hwd / cm)	31.60 x 11.71 x 4.90	
Unit Weight (lbs.)	2.3	
Unit Weight (kg)	1.04	
FEATURES & SPECIFICATIONS		
Rotatable Outlets	No	
Antimicrobial	No	
WARRANTY & SUPPORT		
Product Warranty Period (Worldwide)	Lifetime limited warranty	

1000 Eaton Boulevard Cleveland, OH 44122 United States https://tripplite.eaton.com © 2024 Eaton. All Rights Reserved. Eaton is a registered trademark. All other trademarks are the property of their respective owners.