

# Quick Start Guide

## USB 3.1 Gen 1 Gigabit Ethernet Adapter

Models: U436-06N-GBW, U436-06N-GB, U436-06N-GBW-RA

Este manual esta disponible  
en español en la página de  
Tripp Lite:  
[www.tripplite.com/support](http://www.tripplite.com/support)

Ce manuel est disponible  
en français sur le site Web  
de Tripp Lite :  
[www.tripplite.com/support](http://www.tripplite.com/support)

Русскоязычная версия  
настоящего руководства  
представлена на веб-сайте  
компании Tripp Lite по адресу:  
[www.tripplite.com/support](http://www.tripplite.com/support)

## Product Features

- Add Gigabit Ethernet via the USB Type-C™ port on your smartphone, tablet, Ultrabook or computer
  - USB 3.1 Gen 1 ensures true 10/100/1000 Mbps network speeds
  - Compliant with IEEE 802.3, 802.3u and 802.3ab standards
  - IEEE 802.3az (Energy Efficient Ethernet) compliant
  - Supports twisted-pair crossover detection and auto-correction
  - Supports Wake-on-LAN
  - Compatible with Windows®, Mac® and Chromium operating systems
  - (U436-06N-GBW-RA model only): Right-angle Type-C connector allows for easy connection in tight spaces
- USB Type-C and USB-C™ are trademarks of USB Implementers Forum*

## Package Contents

- U436-06N-GBW (White), U436-06N-GB (Black) or U436-06N-GBW-RA (White, Right-Angle Connector)
- Quick Start Guide

## Installation

1. Connect the adapter's USB Type-C connector to the USB Type-C port on your smartphone, tablet, Ultrabook or computer.
2. Connect the adapter's RJ45 port to a network using a UTP cable (such as Tripp Lite's N201-Series Cat6 cables).

### PROTECT YOUR INVESTMENT!

Register your product for quicker service  
and ultimate peace of mind.

You could also win an ISOBAR6ULTRA  
surge protector—a \$100 value!

[www.tripplite.com/warranty](http://www.tripplite.com/warranty)



**TRIPP-LITE**



1111 W. 35th Street, Chicago, IL 60609 USA  
[www.tripplite.com/support](http://www.tripplite.com/support)

Copyright © 2018 Tripp Lite. All rights reserved.

## Specifications

### Connectors

USB	USB Type-C Male
Ethernet	RJ45 Female

### Environmental

Operating Temperature	32 to 113°F (0 to 45°C)
Operating Humidity	10% to 85% RH, Non-Condensing
Storage Temperature	14 to 158°F (-10 to 70°C)
Storage Humidity	5% to 90% RH, Non-Condensing

### Power Requirements

External Power Supply	No
Power Consumption (Max)	1W

## Warranty and Product Registration

### 3-Year Limited Warranty

TRIPP LITE warrants its products to be free from defects in materials and workmanship for a period of three (3) years from the date of initial purchase. TRIPP LITE's obligation under this warranty is limited to repairing or replacing (at its sole option) any such defective products. To obtain service under this warranty, you must obtain a Returned Material Authorization (RMA) number from TRIPP LITE or an authorized TRIPP LITE service center. Products must be returned to TRIPP LITE or an authorized TRIPP LITE service center with transportation charges prepaid and must be accompanied by a brief description of the problem encountered and proof of date and place of purchase. This warranty does not apply to equipment, which has been damaged by accident, negligence or misapplication or has been altered or modified in any way. EXCEPT AS PROVIDED HEREIN, TRIPP LITE MAKES NO WARRANTIES, EXPRESS OR IMPLIED, INCLUDING WARRANTIES OF MERCHANTABILITY AND FITNESS FOR A PARTICULAR PURPOSE.

### PRODUCT REGISTRATION

Visit [www.tripplite.com/warranty](http://www.tripplite.com/warranty) today to register your new Tripp Lite product. You'll be automatically entered into a drawing for a chance to win a FREE Tripp Lite product!\*

\* No purchase necessary. Void where prohibited. Some restrictions apply. See website for details.

Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice.

Some states do not permit limitation or exclusion of implied warranties; therefore, the aforesaid limitation(s) or exclusion(s) may not apply to the purchaser.

EXCEPT AS PROVIDED ABOVE, IN NO EVENT WILL TRIPP LITE BE LIABLE FOR DIRECT, INDIRECT, SPECIAL, INCIDENTAL OR CONSEQUENTIAL DAMAGES ARISING OUT OF THE USE OF THIS PRODUCT, EVEN IF ADVISED OF THE POSSIBILITY OF SUCH DAMAGE. Specifically, TRIPP LITE is not liable for any costs, such as lost profits or revenue, loss of equipment, loss of use of equipment, loss of software, loss of data, costs of substitutes, claims by third parties, or otherwise.

Use of this equipment in life support applications where failure of this equipment can reasonably be expected to cause the failure of the life support equipment or to significantly affect its safety or effectiveness is not recommended.



1111 W. 35th Street, Chicago, IL 60609 USA • [www.tripplite.com/support](http://www.tripplite.com/support)