


Owner's Manual

Full-Motion Flat-Screen Wall Mount

Model: DWM2355S



WARNING! Always use an assistant or mechanical lifting equipment to safely lift and position equipment.



75x75/100x100
200x100/200x200
300x300/400x200
400x300/400x400



Este manual esta disponible en español en la página de Tripp Lite: tripplite.com

Ce manuel est disponible en français sur le site Web de Tripp Lite : tripplite.com

Русскоязычная версия настоящего руководства представлена на веб-сайте компании Tripp Lite по адресу: tripplite.com

Dieses Handbuch ist in deutscher Sprache auf der Tripp Lite-Website verfügbar: tripplite.com

WARRANTY REGISTRATION

Register your product today and be automatically entered to win an ISOBAR® surge protector in our monthly drawing!
tripplite.com/warranty



1111 W. 35th Street, Chicago, IL 60609 USA • tripplite.com/support

Copyright © 2020 Tripp Lite. All rights reserved.

Important Safety Instructions




CAUTION

- Read the entire instruction manual before you start assembly and installation. If you have questions about any of the instructions or warnings, contact Tripp Lite Support.
- Use with products heavier than the rated weights indicated may result in instability, causing possible injury.
- Mounts must be attached as specified in these instructions. Improper installation may result in damage or serious personal injury.
- Safety gear and proper tools must be used. This product should only be installed by professionals.
- This product is designed to be installed on wood stud walls, solid concrete walls or brick walls.
- Ensure the supporting surface will safely support the combined weight of the equipment and all attached hardware and components.
- Use the mounting screws provided and **DO NOT OVERTIGHTEN** the mounting screws.
- This product contains small items that could be a choking hazard if swallowed. Keep these items away from children.
- This product is intended for indoor use only. Using this product outdoors could lead to product failure and personal injury.
- Check that the bracket is secure and safe to use at regular intervals (at least every three months)


Parts List

IMPORTANT: Before beginning installation, be sure you have received all the parts listed below. If any parts are missing or faulty, contact Tripp Lite for replacements.


Components



A
Wall Plate/
Articulating Arm (x1)



B
VESA Plate (x1)



C
VESA Adapter
Bracket (x4)



D
Wall Plate
End Cap (x1)




E
Wall Plate
End Cap (x1)




F
Nut
(x4)




G
Bolt
(x4)



H
Wrench
(x1)




I
4 mm Hex
Key (x1)




J
6 mm Hex
Key (x1)

Parts List

Package M




M-A
M5x14 (x4)




M-B
M6x14 (x4)



M-C
M6x30 (x4)



M-D
M8x30 (x4)



M-E
M8x50 (x4)




M-F
D6 Washer (x4)



M-G
D8 Washer (x4)



M-H
Smaller Spacer (x8)



M-I
Large Spacer (x8)

Package W



W-A
Anchor Bolt (x3)




W-B
Concrete Anchor (x3)




W-C
Washer (x3)


Required for Installation




Stud finder
(for installation
on wood stud wall)




Pencil



Level








Drill with
appropriate bits
(for installation type)





Screwdriver


1a. Mount on Wood Stud Wall




1
Find and mark the exact location of mounting holes



3
Drill pilot holes



Ensure holes are level







Screw mount into wall




WARNING

- Make sure the mounting screws are anchored into the center of the studs. Use of a stud finder is highly recommended.
- The installer is responsible to provide hardware for other types of mounting situations.
- The installer must verify the supporting surface will safely support the combined load of the equipment and all attached hardware and components.


1b. Mount on Solid Brick or Concrete Block





1
Find and mark the exact location of mounting holes



2
Drill pilot holes



Ensure holes are level




Screw mount into wall




WARNING

- When installing wall mount onto a concrete masonry unit (also known as a CMU or cinder block), verify the actual concrete thickness is at least 1-3/8" (35 mm) in order to hold the concrete anchors. DO NOT DRILL INTO MORTAR JOINTS! Be sure to mount the assembled wall-mount plate with the included concrete anchors, D6 washers and anchor bolts onto solid sections of the blocks. The solid sections can generally be found 1" (25 mm) toward the middle of the block from either end. An electric drill on a slow setting is recommended to drill the hole rather than a hammer drill to avoid breaking out the back of the hole when entering a hollow section.
- The installer must verify the supporting surface will safely support the combined load of the equipment and all attached hardware and components.

2. Install Articulating Arm




3. Prepare VESA Plate




4. Attach VESA Adapter Brackets


4a VESA 300x300mm, 400x400mm



4b VESA 400x200mm, 300x200mm







4c VESA 400x300mm







5. Mount Brackets to Display

5a



5b





Note: Choose appropriate screws, washers and spacers (if necessary) according to the type of screen.

- Position the adapter brackets as close as possible to the center of the display.
- Firmly secure the adapter brackets onto the display using the screws and any other necessary hardware components included with the unit.






DO NOT OVERTIGHTEN SCREWS!


6. Hang Flat Screen onto Articulating Arm




7. Level and Tighten Screen




8. Adjust Articulating Arm



9. Route Cables



10. Adjust Viewing Angle



Warranty and Product Registration

5-Year Limited Warranty

Seller warrants this product, if used in accordance with all applicable instructions, to be free from original defects in material and workmanship for a period of 5 years from the date of initial purchase. If the product should prove defective in material or workmanship within that period, Seller will repair or replace the product, at its sole discretion.

THIS WARRANTY DOES NOT APPLY TO NORMAL WEAR OR TO DAMAGE RESULTING FROM ACCIDENT, MISUSE, ABUSE OR NEGLIGENCE. SELLER MAKES NO EXPRESS WARRANTIES OTHER THAN THE WARRANTY EXPRESSLY SET FORTH HEREIN. EXCEPT TO THE EXTENT PROHIBITED BY APPLICABLE LAW, ALL IMPLIED WARRANTIES, INCLUDING ALL WARRANTIES OF MERCHANTABILITY OR FITNESS, ARE LIMITED IN DURATION TO THE WARRANTY PERIOD SET FORTH ABOVE; AND THIS WARRANTY EXPRESSLY EXCLUDES ALL INCIDENTAL AND CONSEQUENTIAL DAMAGES. (Some states do not allow limitations on how long an implied warranty lasts, and some states do not allow the exclusion or limitation of incidental or consequential damages, so the above limitations or exclusions may not apply to you. This warranty gives you specific legal rights, and you may have other rights which vary from jurisdiction to jurisdiction.)

WARNING: The individual user should take care to determine prior to use whether this device is suitable, adequate or safe for the use intended. Since individual applications are subject to great variation, the manufacturer makes no representation or warranty as to the suitability or fitness of these devices for any specific application.

PRODUCT REGISTRATION

Visit tripplite.com/warranty today to register your new Tripp Lite product. You'll be automatically entered into a drawing for a chance to win a FREE Tripp Lite product!*

* No purchase necessary. Void where prohibited. Some restrictions apply. See website for details.

Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Images may differ slightly from actual products.

