

# Owner's Manual

## HDMI to DisplayPort 1.2 Active Cable

Models: P567-01M, P567-02M

Este manual esta disponible en español en la página  
de Tripp Lite: [tripplite.com](http://tripplite.com)

Ce manuel est disponible en français sur le site Web  
de Tripp Lite : [tripplite.com](http://tripplite.com)

Русскоязычная версия настоящего руководства  
представлена на веб-сайте компании  
Tripp Lite по адресу: [tripplite.com](http://tripplite.com)

Dieses Handbuch ist in deutscher Sprache auf der  
Tripp Lite-Website verfügbar: [tripplite.com](http://tripplite.com)

### WARRANTY REGISTRATION

Register your product today and be automatically  
entered to win an ISOBAR® surge protector  
in our monthly drawing!

[tripplite.com/warranty](http://tripplite.com/warranty)

The logo for Tripp Lite, featuring the brand name in a bold, italicized, sans-serif font. The text is contained within a stylized graphic of two horizontal lines that curve upwards at the ends, resembling a bridge or a stylized 'U' shape.

1111 W. 35th Street, Chicago, IL 60609 USA  
[tripplite.com/support](http://tripplite.com/support)

Copyright © 2021 Tripp Lite. All rights reserved.

## **Product Features**

- DisplayPort 1.2 cable connects an HDMI audio/video source device to a DisplayPort display device
- Supports true 4K video resolutions up to 4096 x 2160 @ 30 Hz
- Supports 7.1-channel surround sound audio
- Bus-powered through USB connection, but USB-A port allows additional power connection if needed
- Plug-and-play operation with no software required for easy, immediate installation

## **Package Contents**

- P567-01M or P567-02M Cable
- Owner's Manual

## **System Requirements**

- Source device (computer, media server, Blu-ray player, etc.) with HDMI output
- Display device (monitor, television, projector) with DisplayPort input

## Installation

**Note:** Make sure all devices you are connecting are powered off before installation.

1. Connect the cable's HDMI plug to the source's HDMI output.
2. Connect the cable's DisplayPort plug to the monitor's DisplayPort input.
3. Power on both the source and the display.
4. **Optional:** If more power is required than the source can provide, connect the built-in USB cable to an available USB-A port on the source.

## Specifications

Specification	Value
Input Ports	HDMI (Male) USB-A (Male: for power only)
Output Port	DisplayPort (Male)
Operating Temperature	32° to 158°F / 0° to 70°C
Storage Temperature	14° to 176°F / -10° to 80°C
Operating Humidity	10 to 85% RH, Non-Condensing
Storage Humidity	5 to 90% RH, Non-Condensing
Max Video Resolutions	4096 x 2160 @ 30 Hz

## Warranty and Product Registration

### 2-Year Limited Warranty

Seller warrants this product, if used in accordance with all applicable instructions, to be free from original defects in material and workmanship for a period of 2 years from the date of initial purchase. If the product should prove defective in material or workmanship within that period, Seller will repair or replace the product, at its sole discretion.

THIS WARRANTY DOES NOT APPLY TO NORMAL WEAR OR TO DAMAGE RESULTING FROM ACCIDENT, MISUSE, ABUSE OR NEGLIGENCE. SELLER MAKES NO EXPRESS WARRANTIES OTHER THAN THE WARRANTY EXPRESSLY SET FORTH HEREIN. EXCEPT TO THE EXTENT PROHIBITED BY APPLICABLE LAW, ALL IMPLIED WARRANTIES, INCLUDING ALL WARRANTIES OF MERCHANTABILITY OR FITNESS, ARE LIMITED IN DURATION TO THE WARRANTY PERIOD SET FORTH ABOVE; AND THIS WARRANTY EXPRESSLY EXCLUDES ALL INCIDENTAL AND CONSEQUENTIAL DAMAGES. (Some states do not allow limitations on how long an implied warranty lasts, and some states do not allow the exclusion or limitation of incidental or consequential damages, so the above limitations or exclusions may not apply to you. This warranty gives you specific legal rights, and you may have other rights which vary from jurisdiction to jurisdiction.)

**WARNING:** The individual user should take care to determine prior to use whether this device is suitable, adequate or safe for the use intended. Since individual applications are subject to great variation, the manufacturer makes no representation or warranty as to the suitability or fitness of these devices for any specific application.

### PRODUCT REGISTRATION

Visit [tripplite.com/warranty](http://tripplite.com/warranty) today to register your new Tripp Lite product. You'll be automatically entered into a drawing for a chance to win a FREE Tripp Lite product!\*

\* No purchase necessary. Void where prohibited. Some restrictions apply. See website for details.

Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Photos and illustrations may differ slightly from actual products.



1111 W. 35th Street, Chicago, IL 60609 USA  
[tripplite.com/support](http://tripplite.com/support)