

Owner's Manual

Wireless Car Charger with USB-C, Auto-Clamp, 15W Qi Charging, Windshield/Dash/Vent Phone Holder

Model: U280-CQ01

Este manual esta disponible en español en la página
de Tripp Lite: triplite.com

Ce manuel est disponible en français sur le site Web
de Tripp Lite : triplite.com

Русскоязычная версия настоящего руководства представлена
на веб-сайте компании Tripp Lite по адресу: triplite.com

PROTECT YOUR INVESTMENT!

Register your product for quicker service and ultimate peace of mind.
You could also win an ISOBAR6ULTRA surge protector—a \$100 value!
triplite.com/warranty



1111 W. 35th Street, Chicago, IL 60609 USA
triplite.com/support

Copyright © 2020 Tripp Lite. All rights reserved.

Product Features



- Qi technology optimizes your charging capabilities when used with the latest Quick Charge (QC) compliant 2.0/3.0 adapters
 - Adjustable arms effortlessly secure and release your Qi-enabled device by tapping the smart-touch buttons
 - Anti-slip silicon pads on adjustable arms keep your device secure when encountering bumps or uneven road surfaces
 - USB-C supports inputs of 5V 2A, 9V 1.67A, 12V 1.5A
 - Wireless charging coil supports output up to 15W
 - Built-in protection technology prevents over-heating, over-charging and short circuits
 - Universally compatible with all Qi-compatible smartphones and devices*
- * Compatible with Apple iPhone 11/11 Pro/11 Pro Max/XS Max/XR/XS/X/8/8 Plus and Samsung Galaxy S10/S10 Plus/S10E/S9/S9 Plus/S8/S8 Plus/Note 9/Note 8/S7/S7 Edge/S6 Edge Plus/Note 5.

Package Includes



- Wireless Car Charger
- Windshield/Dashboard Mounting Stand
- Vent Mounting Clip
- USB-A to USB-C Cable, 3.3 ft.
- Owner's Manual

Assembly

Windshield/Dashboard




Air Vent




Installation



Windshield/Dashboard



Dashboard Surface



Air Vent



Operation

Notes:

- To achieve high-speed charging capabilities (up to 7.5W for Apple devices and 10W for Samsung devices), Quick Charge (QC) 2.0/3.0 adapters are recommended.
- Phone cases thicker than 5 mm may result in slower charging speeds.
- Magnetic or metal attachments will prevent charging.
- Compatible with Apple iPhone 11/11 Pro/11 Pro Max/XS Max/XR/XS/X/8/8 Plus and Samsung Galaxy S10/S10 Plus/S10E/S9/S9 Plus/S8/S8 Plus/Note 9/Note 8/S7/S7 Edge/S6 Edge Plus/Note 5.

1. Using the included USB-A to USB-C cable, connect the wireless charger to a USB-A power adapter.

Note: QC 2.0/3.0 power adapters are recommended.

- 2 Once connected to power, the LEDs surrounding the smart-touch buttons will turn green to indicate the charger is in standby mode.
3. Tap either smart-touch button located on each side of the charger to open the two adjustable arms. Place your phone on the charger. In doing so, the two arms will automatically secure the phone. The two blue LEDs located on each side of the charger will illuminate solid to indicate the phone is charging wirelessly.

Note: Foreign Body Detection (FBD) occurs when metal or magnetic objects are placed on the charger. The smart-touch button LEDs will flash blue 6x before cutting off power to the charger.

4. To remove the phone from the charger, touch either smart-touch button located on each side of the charger to open the two adjustable arms.

Specifications

Input	USB-C USB: 5V/2A, 9V/1.67A, 12V/1.5A
Output	5W, 7.5W, 10W, 15W
Qi Compatible	Yes
Switch Frequency	110 kHz to 205 kHz
Operating Temperature Range	32°F to 104°F / 0°C to 40°C
Storage Temperature Range	14°F to 122°F / -10°C to 50°C
Operating Humidity Range	10% to 80% RH, Non-Condensing
Storage Humidity Range	5% to 95% RH, Non-Condensing
Max Output for Apple iPhone	Up to 7.5W
Max Output for Samsung Galaxy	Up to 10W
Dimensions (H x W x D)	4.8 x 2.8 x 2 in. / 121 x 74 x 52 mm
Weight	0.45 lb. / 0.2 kg

Warranty and Product Registration

2-Year Limited Warranty

TRIPP LITE warrants its products to be free from defects in materials and workmanship for a period of one (2) years from the date of initial purchase. TRIPP LITE's obligation under this warranty is limited to repairing or replacing (at its sole option) any such defective products. To obtain service under this warranty, you must obtain a Returned Material Authorization (RMA) number from TRIPP LITE or an authorized TRIPP LITE service center. Products must be returned to TRIPP LITE or an authorized TRIPP LITE service center with transportation charges prepaid and must be accompanied by a brief description of the problem encountered and proof of date and place of purchase. This warranty does not apply to equipment, which has been damaged by accident, negligence or misapplication or has been altered or modified in any way.

EXCEPT AS PROVIDED HEREIN, TRIPP LITE MAKES NO WARRANTIES, EXPRESS OR IMPLIED, INCLUDING WARRANTIES OF MERCHANTABILITY AND FITNESS FOR A PARTICULAR PURPOSE.

Some states do not permit limitation or exclusion of implied warranties; therefore, the aforesaid limitation(s) or exclusion(s) may not apply to the purchaser.

EXCEPT AS PROVIDED ABOVE, IN NO EVENT WILL TRIPP LITE BE LIABLE FOR DIRECT, INDIRECT, SPECIAL, INCIDENTAL OR CONSEQUENTIAL DAMAGES ARISING OUT OF THE USE OF THIS PRODUCT, EVEN IF ADVISED OF THE POSSIBILITY OF SUCH DAMAGE. Specifically, TRIPP LITE is not liable for any costs, such as lost profits or revenue, loss of equipment, loss of use of equipment, loss of software, loss of data, costs of substitutes, claims by third parties, or otherwise.

PRODUCT REGISTRATION

Visit www.tripp-lite.com/warranty today to register your new Tripp Lite product. You'll be automatically entered into a drawing for a chance to win a FREE Tripp Lite product!*

* No purchase necessary. Void where prohibited. Some restrictions apply. See website for details.

WEEE Compliance Information for Tripp Lite Customers and Recyclers (European Union)



Under the Waste Electrical and Electronic Equipment (WEEE) Directive and implementing regulations, when customers buy new electrical and electronic equipment from Tripp Lite they are entitled to:

- Send old equipment for recycling on a one-for-one, like-for-like basis (this varies depending on the country)
- Send the new equipment back for recycling when this ultimately becomes waste

WARNING

Use of this equipment in life support applications where failure of this equipment can reasonably be expected to cause the failure of the life support equipment or to significantly affect its safety or effectiveness is not recommended.

Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Photos and illustrations may differ slightly from actual products.



1111 W. 35th Street, Chicago, IL 60609 USA • tripplite.com/support