

Owner's Manual

USB 3.1 USB-C™ Multi-Port Clip Dock with PD Charging, HDMI, Audio & Card Readers

Model: U442-DOCK15-S

Este manual esta disponible en español en la página de
Tripp Lite: tripplite.com/support

Ce manuel est disponible en français sur le site Web de
Tripp Lite : tripplite.com/support

Русскоязычная версия настоящего руководства представлена на веб-сайте
компании Tripp Lite по адресу: tripplite.com

WARRANTY REGISTRATION

Register your product today and be
automatically entered to win an ISOBAR
surge protector in our monthly drawing!

tripplite.com/warranty



1111 W. 35th Street, Chicago, IL 60609 • tripplite.com/support

Copyright © 2019 Tripp Lite. All rights reserved.

Product Features

- On-the-go docking station connects to a USB-C port to give your device HDMI video, audio, data and memory card ports.
- USB-C Power Delivery (PD) 3.0 port provides up to 60W of power to your USB-C enabled device.
- Sends crystal-clear 4K x 2K @ 30 Hz video signals to a 4K-enabled HDMI TV or projector.
- USB 2.0 Type-A port supports data transfer speeds up to 480 Mbps and is backward compatible with USB 1.1.
- SD and Micro SD memory card slots can be used simultaneously and support 5 Gbps transfer speeds.
- Listen to music or record a podcast using the available 3.5 mm audio port.
- HDMI 1.4 and HDCP 1.4 compliant.
- Plug-and-play design, no external power or drivers needed.


Package Contents

- U442-DOCK15-S
- Owner's Manual

Optional Accessories:


- P312-Series 3.5 mm Mini Stereo Audio Cables
- P569-Series High Speed HDMI Cables
- U050-XXX-GY-MAX Heavy Duty USB-A to USB Micro-B Cables

Product Overview



- 1 HDMI Port:** Supports resolutions up to 4K x 2K (3840 x 2160) @ 30 Hz
- 2 USB-C Port:** Supports PD 3.0 Charging up to 60W (20V/3A)
- 3 3.5 mm Audio Port:** Supports audio output and microphone input
- 4 Micro SD Card Slot**
- 5 SD Card Slot**
- 6 LED:** Illuminates white when power is supplied
- 7 USB 2.0 Type A:** Supports data transfer rates up to 480 Mbps
- 8 USB 3.1 Type C (Male)**

Installation



- 1** Connect the USB 3.1 Type-C male connector to your USB-C enabled device.
Note: Insert until the clip is fully secured to your device or until a click is heard.
- 2** Using an HDMI cable, such as Tripp Lite's P569-Series (sold separately), connect the HDMI port to your monitor, TV or projector.
- 3** Connect your USB-C device's power supply or adapter to the available USB-C PD 3.0 port.
- 4** Connect headphones or a microphone to the 3.5 mm port.
- 5** Insert an SD or Micro SD memory card into the corresponding slot to access external memory.
Note: Both memory card slots can be used simultaneously.
- 6** Transfer data up to 480 Mbps using the USB 2.0 Type-A port.

Specifications:

Input Connector	
USB-C	(x1) USB 3.1 Type-C (Male)
Output Connectors	
USB-A	(x1) USB 2.0
USB-C	(x1) USB-C PD Charging Only
HDMI	HDMI
Audio	3.5 mm
Memory Cards	(x1) SD, (x1) Micro SD
Environmental	
Operating Temperature	32°F to 122°F (0°C to 50°C)
Operating Humidity	10 to 90% RH, Non-Condensing
Storage Temperature	-4°F to 158°F (-20°C to 70°C)
Storage Humidity	0 to 95% RH, Non-Condensing
Mechanical	
Unit Dimensions	1.3 x 3.9 x 0.5 in. (33 x 99 x 12.7 mm)
Unit Weight	0.1 lb. (0.05 kg)
Specifications	
HDMI Specification	1.4
HDCP Specification	1.4
Max Supported Video Resolution(s)	HDMI: 3840 x 2160 @ 30 Hz
Support Color Depth (HDMI)	36 bit (12 bits per channel)
Chroma Subsampling (HDMI)	YCbCr: 4:4:4, 4:2:2, 4:2:0
Audio Specifications	Stereo Audio and Microphone Input
PD Charging Specification	PD 3.0 (60W)

Warranty & Product Registration

3-Year Limited Warranty

TRIPP LITE warrants its products to be free from defects in materials and workmanship for a period of three (3) years from the date of initial purchase. TRIPP LITE's obligation under this warranty is limited to repairing or replacing (at its sole option) any such defective products. To obtain service under this warranty, you must obtain a Returned Material Authorization (RMA) number from TRIPP LITE or an authorized TRIPP LITE service center. Products must be returned to TRIPP LITE or an authorized TRIPP LITE service center with transportation charges prepaid and must be accompanied by a brief description of the problem encountered and proof of date and place of purchase. This warranty does not apply to equipment which has been damaged by accident, negligence or misapplication or has been altered or modified in any way.

EXCEPT AS PROVIDED HEREIN, TRIPP LITE MAKES NO WARRANTIES, EXPRESS OR IMPLIED, INCLUDING WARRANTIES OF MERCHANTABILITY AND FITNESS FOR A PARTICULAR PURPOSE. Some states do not permit limitation or exclusion of implied warranties; therefore, the aforesaid limitation(s) or exclusion(s) may not apply to the purchaser.

EXCEPT AS PROVIDED ABOVE, IN NO EVENT WILL TRIPP LITE BE LIABLE FOR DIRECT, INDIRECT, SPECIAL, INCIDENTAL OR CONSEQUENTIAL DAMAGES ARISING OUT OF THE USE OF THIS PRODUCT, EVEN IF ADVISED OF THE POSSIBILITY OF SUCH DAMAGE. Specifically, TRIPP LITE is not liable for any costs, such as lost profits or revenue, loss of equipment, loss of use of equipment, loss of software, loss of data, costs of substitutes, claims by third parties, or otherwise.

Product Registration

Visit tripplite.com/warranty today to register your new Tripp Lite product. You'll be automatically entered into a drawing for a chance to win a FREE Tripp Lite product!*

* No purchase necessary. Void where prohibited. Some restrictions apply. See website for details.

FCC Notice, Class B

This device complies with part 15 of the FCC Rules. Operation is subject to the following two conditions: (1) This device may not cause harmful interference, and (2) this device must accept any interference received, including interference that may cause undesired operation.

Warranty & Product Registration

Note: This equipment has been tested and found to comply with the limits for a Class B digital device, pursuant to part 15 of the FCC Rules. These limits are designed to provide reasonable protection against harmful interference in a residential installation. This equipment generates, uses and can radiate radio frequency energy and, if not installed and used in accordance with the instructions, may cause harmful interference to radio communications. However, there is no guarantee that interference will not occur in a particular installation. If this equipment does cause harmful interference to radio or television reception, which can be determined by turning the equipment off and on, the user is encouraged to try to correct the interference by one or more of the following measures:

- Reorient or relocate the receiving antenna.
- Increase the separation between the equipment and receiver.
- Connect the equipment into an outlet on a circuit different from that to which the receiver is connected.
- Consult the dealer or an experienced radio/TV technician for help.

Any changes or modifications to this equipment not expressly approved by Tripp Lite could void the user's authority to operate this equipment.

WEEE Compliance Information for Tripp Lite Customers and Recyclers (European Union)



Under the Waste Electrical and Electronic Equipment (WEEE) Directive and implementing regulations, when customers buy new electrical and electronic equipment from Tripp Lite they are entitled to:

- Send old equipment for recycling on a one-for-one, like-for-like basis (this varies depending on the country)
- Send the new equipment back for recycling when this ultimately becomes waste

Use of this equipment in life support applications where failure of this equipment can reasonably be expected to cause the failure of the life support equipment or to significantly affect its safety or effectiveness is not recommended.

Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Photos and illustrations may differ slightly from actual products.



Manufacturing
Excellence.

1111 W. 35th Street, Chicago, IL 60609 • tripplite.com/support