

Introducing the First Medical-Grade Power Strip with Full UL 60601-1/60950-1 Compliance

Tripp Lite's NEW PS-415-HGULTRA Power Strip replaces **ALL** of your current outlet strips (including those with hospital-grade plugs and receptacles)—helping bring your facility into full compliance with major safety regulations!

- First power strip of its kind to comply with major safety regulations required for **ALL** medical facilities—fully tested, certified and compliant to UL 60601-1 and UL 60950-1*
- Designed for use in a variety of medical facilities (physician's offices, imaging centers, laboratories and more) including where NEC requires hospital-grade receptacles
- Unique, patent-pending, internal site-wiring fault protection resets automatically
- 4 hospital-grade outlets with safety covers
- 15 ft. AC power cord with hospital-grade plug
- Switchless design prevents accidental shutoff

*These standards govern the use of electrical and IT-related equipment in medical environments.


PS-415-HGULTRA Specifications

Electrical Compatibility:	120VAC (50/60 Hz)
Load:	15A
Outlets:	4 NEMA 5-15RHG with safety covers
Outlet Format:	Single row of 4
Overload Protection:	15A circuit breaker
Input Connection:	NEMA 5-15PHG plug
Cord Length:	15 ft.
Housing Construction:	Metal
Color:	White
Unit Dimensions (H x W x D, in):	1.5 x 13.75 x 2.5
Unit Weight (lb):	3.2
Product Warranty:	Lifetime

Tested to U.S. and Canadian Standards



USA: TUV tested to UL 60601-1 and UL 60950-1
 Canada (CSA): TUV tested to CAN/CSA-C22.2 No. 601.1-M90 and 60950-1-03



Hospital-grade plug.
Optional-use keyhole mounting slots and flanges.

Add AC Power to Your Medical Carts

Tripp Lite's NEW Medical-Grade, Mobile-Power Retrofit Kits add battery-supplied AC power to most standard medical carts while providing UL 60601-1 compliance for connected equipment.

For more information: Contact Tripp Lite
(773) 869-1282 or medical@tripplite.com



TRIPP-LITE

POWER PROTECTION

www.tripplite.com

1111 W. 35th Street • Chicago, IL 60609