

# 2-Port Manual VGA/SVGA Video Switch (3x HD15F)

MODEL NUMBER: B112-002-R



### Highlights

- 2-port HD15 VGA/SVGA Push-Button Switch
- Rugged Metal Case

### System Requirements

- Computer with an HD15 port
- VGA or SVGA monitor with HD15M cable

### Package Includes

- B112-002-R Manual VGA/SVGA 2 Position Switch

### Description

This 2-Port Manual VGA/SVGA Switch is the optimal solution for connecting two computers to one monitor or two monitors to one computer. The 2-Port Manual VGA/SVGA Switch features a fully shielded rugged metal case with front-panel push-button switching. Interior printed circuit board design allows for crystal clear resolutions up to 1600 x 1280. It does not require any AC power to operate.

### Features

- Connects two computers to one monitor or two monitors to one computer
- Fully-shielded rugged metal case with front-panel push button switch
- Does not require external power, software, or complicated set-up procedures

## Specifications

OVERVIEW	
UPC Code	037332014269
Technology	VGA/SVGA
VIDEO	
Max Supported Video Resolution	1920 x 1080 @ 60Hz
HDR Support	No
INPUT	
Bus Powered	Yes
Product Length (in.)	4.41
Product Length (ft.)	0.37



Powering Business Worldwide



POWER	
Power Consumption (Watts)	0.5
CONNECTIONS	
Number of Ports	2
Side A - Connector 1	(2) HD15 (FEMALE)
Side B - Connector 1	HD15 (FEMALE)
Connector Plating	Nickel
Input x Output	2 x 1
PHYSICAL	
Color	Silver
Material of Construction	Aluminum
Rackmountable	No
Shipping Dimensions (hwd / in.)	4.53 x 1.06 x 3.27
Shipping Dimensions (hwd / cm)	11.51 x 2.69 x 8.31
Shipping Weight (lbs.)	3.53
Shipping Weight (kg)	1.60
Unit Dimensions (hwd / in.)	0.940 x 4.400 x 2.700
Unit Packaging Type	Box
Unit Weight (lbs.)	0.33
Unit Weight (kg)	0.15
ENVIRONMENTAL	
Operating Temperature Range	14° to 131°F (-10° to 55°C)
Storage Temperature Range	5° to 131°F (-15° to 55°C)
Relative Humidity	5% to 90% RH, Non-Condensing
BTUs	1.7 BTU/Hr
COMMUNICATIONS	
EDID Compatible	Yes
IR Remote Extension Support	No
FEATURES & SPECIFICATIONS	
Port Selection	Pushbutton
Driver Required	No
STANDARDS & COMPLIANCE	



Powering Business Worldwide



Product Compliance	RoHS; CE (Europe); REACH; FCC (USA)
<b>WARRANTY &amp; SUPPORT</b>	
Product Warranty Period (Worldwide)	1-year limited warranty

1000 Eaton Boulevard  
Cleveland, OH 44122  
United States  
<https://tripplite.eaton.com>

© 2024 Eaton. All Rights Reserved.  
Eaton is a registered trademark. All other trademarks  
are the property of their respective owners.