

Full-Motion Wall-Mount Swivel Arm for 17" to 42" Flat-Screen Displays

MODEL NUMBER: DWM1737S



Highlights

- SEE NEW MODEL - DWM1742S
- Can be used to increase available desk/table space in office applications
- Fits most flat-panel displays from 17" to 42"
- Convenient one-touch display adjustment for easy view optimization
- Wide range of motion with -15° to +15° tilt, 180° swivel and -3° to +3° screen level adjustment capability
- Supports up to 44 lbs.
- 5-year warranty

Package Includes

- DWM1737S Full-Motion Flat-Screen Wall Mount
- Mounting Hardware
- Owner's Manual

Description

Tripp Lite's VESA-compliant DWM1737S Full-Motion Flat-Screen Wall Mount offers full-motion articulation and can free up valuable space in your workstation by allowing you to effortlessly reposition your display at any time, even after installation. Its sleek design features convenient one-touch display adjustment with tilt and swivel capabilities and fits most 17- to 42-inch flat-panel displays. Its durable, all-metal frame with soft, rubber feel finish withstands the stress of repeated use and blends easily into any décor. It comes with all necessary mounting hardware and supports weights of up to 44 lb. For peace of mind, the DWM1737S comes backed by a 5-year warranty.

Features

- Tripp Lite's VESA-compliant DWM1737S Full-Motion Flat-Screen Wall Mount offers full-motion articulation and can free up valuable space in your workstation by allowing you to effortlessly reposition your display at any time, even after installation
- Sleek design features convenient one-touch display adjustment with tilt and swivel capabilities
- Fits most 17- to 42-inch flat-panel displays
- Durable, all-metal frame with soft, rubber feel finish withstands the stress of repeated use and blends easily into any décor
- Comes with all necessary mounting hardware and supports weights of up to 44 lbs
- 5-year warranty

Specifications

| OVERVIEW | |
|----------|---------------|
| UPC Code | 037332178718 |
| PHYSICAL | |
| Color | Black; Silver |



Powering Business Worldwide



| | |
|---|--|
| Material of Construction | Metal |
| VESA Pattern (mm) | 100x100; 200x100; 200x200 |
| Motion | Full |
| Mounting Location | Wall |
| Degrees of Motion | -15/+15 Tilt; 180 Swivel; -3/+3 Level Adjustment |
| Maximum Weight Capacity (lbs.) | 44 |
| Maximum Weight Capacity (kg) | 20 |
| Shipping Dimensions (hwd / in.) | 3.70 x 19.50 x 15.70 |
| Shipping Dimensions (hwd / cm) | 9.40 x 49.53 x 39.88 |
| Shipping Weight (lbs.) | 10.30 |
| Shipping Weight (kg) | 4.67 |
| Unit Dimensions (hwd / in.) | 7.480 x 22.870 x 9.050 |
| Unit Weight (lbs.) | 10.51 |
| Unit Weight (kg) | 4.77 |
| FEATURES & SPECIFICATIONS | |
| Cord Management | No |
| Tools Necessary | Yes |
| WARRANTY & SUPPORT | |
| Product Warranty Period (Worldwide) | 5-year limited warranty |
| Product Warranty Period (U.S. & Canada) | 5-year limited warranty |

1000 Eaton Boulevard
Cleveland, OH 44122
United States
<https://tripplite.eaton.com>

© 2024 Eaton. All Rights Reserved.
Eaton is a registered trademark. All other trademarks
are the property of their respective owners.