

Fixed Wall-Mount for 26" to 55" Flat-Screen Displays

MODEL NUMBER: DWF2647X



Description

Tripp Lite's VESA-compliant DWF2647X Fixed Flat-Screen Wall Mount's low-profile design features an open frame for easy wall access and optimal display positioning flexibility. Its durable, all-metal construction with scratch-resistant, powder-coat finish supports weights of up to 165 lbs. and fits most 26- to 55-inch flat-panel displays. It comes with all necessary mounting hardware and features horizontal adjustment to compensate for off-center wall studs. A built-in bubble level enables accurate display leveling. For peace of mind, the DWF2647X comes backed by a 5-year warranty and green, RoHS-compliant design.

Features

- VESA-compliant DWF2647X Fixed Flat-Screen Wall Mount's low-profile design features an open frame for easy wall access and optimal display positioning flexibility
- Durable, all-metal construction with scratch-resistant, powder-coat finish supports weights of up to 165 lbs. and fits most 26- to 55-inch flat-panel displays
- Includes all necessary mounting hardware and features horizontal adjustment to compensate for off-center wall studs
- A built-in bubble level enables accurate display leveling
- 5-year warranty
- Green, RoHS-compliant design

Highlights

- **SEE NEW MODEL - DWF2655X**
- Low-profile mounting keeps unit out of sight for sleek, professional appearance
- Fits most flat-panel displays from 26" to 55"
- Open frame for easy wall access
- Horizontal adjustment compensates for off-center wall studs
- Equipped with a bubble level for accurate display leveling
- Supports up to 165 lb
- 5-year warranty

Package Includes

- DWF2647X Fixed Flat-Screen Wall Mount
- Mounting Hardware
- Owner's Manual

Specifications

OVERVIEW	
UPC Code	037332178770
PHYSICAL	
Color	Black



Powering Business Worldwide



Material of Construction	Metal
VESA Pattern (mm)	100x100; 200x100; 200x200; 400x200; 400x400
Motion	Fixed
Mounting Location	Wall
Degrees of Motion	Fixed
Maximum Weight Capacity (lbs.)	165
Maximum Weight Capacity (kg)	75
Shipping Dimensions (hwd / in.)	19.49 x 4.72 x 1.77
Shipping Dimensions (hwd / cm)	49.50 x 11.99 x 4.50
Shipping Weight (lbs.)	4.51
Shipping Weight (kg)	2.05
Unit Dimensions (hwd / in.)	17.130 x 18.260 x 1.180
Unit Weight (lbs.)	4.51
Unit Weight (kg)	2.05
FEATURES & SPECIFICATIONS	
Cord Management	No
Tools Necessary	Yes
WARRANTY & SUPPORT	
Product Warranty Period (Worldwide)	5-year limited warranty
Product Warranty Period (U.S. & Canada)	5-year limited warranty

1000 Eaton Boulevard
 Cleveland, OH 44122
 United States
<https://tripplite.eaton.com>

© 2024 Eaton. All Rights Reserved.
 Eaton is a registered trademark. All other trademarks
 are the property of their respective owners.