

## Cat6 Gigabit Molded (UTP) Ethernet Cable (RJ45 M/M), PoE, Black, 10 ft. (3.05 m)

MODEL NUMBER: N200-010-BK



Ideal for connecting high-speed network components, such as computers, printers, video game systems, Blu-ray™ players, copy machines, routers and modems, in a home or office Cat5/5e/6 application.

### Description

The N200-010-BK Cat6 Gigabit Molded Patch Cable (M/M) ensures ultra-fast performance throughout your Cat5/5e/6 network application. It connects high-speed network components like computers, printers, video game systems, Blu-ray players, copy machines, routers and modems in a home or office Cat5/5e/6 application.

This 10-ft. (3.05 m) black cable is designed for 1000Base-T (1 Gbps Ethernet), 10/100Base-T (Ethernet), 100 Mbps TPDDI, 155 Mbps ATM, ISDN, voice, Token Ring Type 3 and EIA/TIA applications.

Manufactured from 24 AWG 4-pair stranded UTP with a staggered-pin plug design and male RJ45 connectors, each cable provides high-speed connections up to 550 MHz/1 Gbps and flawless signal delivery, while keeping near-end crosstalk levels to a minimum.

The N200-010-BK is constructed of top-quality materials for long life and durability. Corrosion-resistant gold-plated copper contacts provide maximum conductivity and minimize data loss. Integral strain relief gives the cable extra flexibility, reduces stress, and helps the cable and connectors move freely without cracking. Meets most current industry standards, including IEEE 802.3ab, IEEE 802.5, ANSI/EIA/TIA 568, ISO/IEC 11801 and ETL (category 6 draft 11).

### Features

#### The Ideal Solution for All High-Speed Cat5/5e/6 Networking

- Connects high-speed network components, such as computers, printers, video game systems, Blu-ray players, copy machines, routers and modems
- Designed for 1000Base-T, 10/100Base-T (Ethernet), 100 Mbps TPDDI, 155 Mbps ATM, ISDN, voice, Token Ring Type 3 and EIA/TIA applications
- Recommended for home or office applications
- Provides high-speed connections up to 550 MHz/1 Gbps
- Flawless signal delivery with minimal near-end crosstalk levels

#### Premium Construction Ensures Error-Free Signal Transfer

- Manufactured from 24 AWG 4-pair stranded UTP with staggered-pin plug design
- Molded RJ45 connectors and gold-plated copper contacts for maximum conductivity and minimum data loss
- Integral strain relief protects cable and connectors from stress and cracking

### Highlights

- Premium cabling for Cat5/5e/6 home/office network applications
- Rated for 550 MHz/1 Gbps communication
- 24 AWG 4-pair stranded UTP with PVC jacket
- Gold-plated copper contacts minimize data loss
- Integral strain relief protects connectors from stress and cracking

### Package Includes

- N200-010-BK Cat6 Gigabit Molded Patch Cable, Black, 10-ft. (3.05 m)



Powering Business Worldwide

TRIPP LITE  
SERIES

- Meets most current industry standards, including IEEE 802.3ab, IEEE 802.5, ANSI/EIA/TIA 568, ISO/IEC 11801 and ETL (category 6 draft 11)

## Specifications

| OVERVIEW                        |                                 |
|---------------------------------|---------------------------------|
| UPC Code                        | 037332194510                    |
| Technology                      | Cat6; PoE                       |
| POWER                           |                                 |
| Power Over Cable (PoC) Support  | No                              |
| CONNECTIONS                     |                                 |
| PoE Capability                  | 30W (802.3at)                   |
| Side A - Connector 1            | RJ45 (MALE)                     |
| Side B - Connector 1            | RJ45 (MALE)                     |
| Crossover Wiring                | No                              |
| Contact Plating                 | Gold                            |
| PoE Type                        | Type 2 PoE+ (30W, IEEE 802.3at) |
| Connector Type                  | Molded                          |
| Wiring Configuration            | EIA/TIA 568B                    |
| Angled Connector                | No                              |
| PHYSICAL                        |                                 |
| Cable Jacket Color              | Black                           |
| Cable Jacket Material           | PVC                             |
| Cable Jacket Rating             | CM                              |
| Cable Shielding                 | UTP                             |
| Cable Outer Diameter (OD)       | 6.0 mm                          |
| Number of Conductors            | 4 Pair                          |
| Conductor Material              | Stranded Copper                 |
| Conductor Gauge                 | 24 AWG                          |
| Cable Length (ft.)              | 10                              |
| Cable Length (m)                | 3.05                            |
| Cable Length (in.)              | 120                             |
| Cable Length (cm)               | 304.8                           |
| Shipping Dimensions (hwd / in.) | 7.00 x 9.00 x 0.50              |
| Shipping Dimensions (hwd / cm)  | 17.78 x 22.86 x 1.27            |



Powering Business Worldwide

TRIPP LITE  
SERIES

|                                      |   |
|--------------------------------------|---|
| Shipping Weight (lbs.)               | 0.29  |
| Shipping Weight (kg)                 | 0.13  |
| <b>ENVIRONMENTAL</b>                 |   |
| Operating Temperature Range          | 14° to 104°F (-10° to 40°C)   |
| Storage Temperature Range            | 5° to 122°F (-15° to 50°C)  |
| Operating Humidity Range             | 0% to 90% RH, Non-Condensing  |
| Storage Humidity Range               | 0% to 90% RH, Non-Condensing  |
| <b>COMMUNICATIONS</b>                |   |
| Bandwidth per TIA Standard           | 250 MHz   |
| Maximum Bandwidth as Tested          | 500 MHz   |
| Network Compatibility                | 1 Gbps (Gigabit)  |
| IEEE Standards Supported             | 802.3an; 802.3at  |
| <b>FEATURES &amp; SPECIFICATIONS</b> |   |
| Antibacterial                        | No  |
| IP68 Rated                           | No  |
| Snagless Connector                   | No  |
| IP20 Rated                           | No  |
| <b>STANDARDS &amp; COMPLIANCE</b>    |   |
| Product Certifications               | UL Listed; cUL Listed   |
| Product Compliance                   | CE (Europe); RoHS; IEEE 802.3an 10GBase-T; IEEE 802.3at PoE+; REACH; UKCA |
| <b>WARRANTY &amp; SUPPORT</b>        |   |
| Product Warranty Period (Worldwide)  | Lifetime limited warranty   |

1000 Eaton Boulevard  
Cleveland, OH 44122  
United States  
<https://tripplite.eaton.com>

© 2024 Eaton. All Rights Reserved.  
Eaton is a registered trademark. All other trademarks  
are the property of their respective owners.