

## Cat6 Gigabit Snagless Slim UTP Ethernet Cable (RJ45 M/M), PoE, Blue, 2 ft. (0.61 m)

MODEL NUMBER: N201-S02-BL



Connects network components like printers, computers, copiers, routers, servers, modems and switches. Ideal for high-density data centers. Slim design increases airflow in tight spaces.

### Features

#### Perfect Solution for Your Networking Needs

- Ideal for connecting components like printers, computers, copiers, routers, servers, modems and switches in high-density data centers
- Designed for fast transmission and excellent signal quality
- Ensures peak performance throughout your LAN
- Delivers speeds up to Cat6 Gigabit/1 Gbps

#### Special Slim Design

- More than 38% smaller in diameter than standard Cat6 cable
- Increases airflow in tight spaces
- Extra flexible for installing around corners and through cable management panels

#### Premium Construction for Superior Performance

- Made from 28 AWG copper wire
- PVC 4-pair stranded UTP
- RJ45 male connectors
- Integral strain relief for long life

#### Snagless Connectors

- snagless boots prevent locking tabs from damage

## Specifications

### Highlights

- Over 38% slimmer than standard Cat6 cables
- Rated for Cat6 Gigabit/1 Gbps communications
- Snagless RJ45 male connectors
- Easy to route through cable management panels
- High-quality 28 AWG copper wire

### Package Includes

- N201-S02-BL Cat6 Gigabit Snagless Slim UTP Patch Cable (RJ45 M/M), 2 ft.



Powering Business Worldwide

TRIPP LITE  
SERIES

|                                    |   |
|------------------------------------|---|
| UPC Code                           | 037332193049  |
| Technology                         | Cat6  |
| <b>CONNECTIONS</b>                 |   |
| Side A - Connector 1               | RJ45 (MALE)   |
| Side B - Connector 1               | RJ45 (MALE)   |
| Crossover Wiring                   | No  |
| Contact Plating                    | Gold  |
| PoE Type                           | Type 1 PoE (15.4W, IEEE 802.3af); Type 2 PoE+ (30W, IEEE 802.3at) |
| Connector Type                     | Snagless  |
| Wiring Configuration               | EIA/TIA 568B  |
| Angled Connector                   | No  |
| <b>PHYSICAL</b>                    |   |
| Cable Jacket Color                 | Blue  |
| Cable Jacket Material              | PVC   |
| Cable Jacket Rating                | CM  |
| Cable Shielding                    | UTP   |
| Cable Outer Diameter (OD)          | 3.8 mm  |
| Number of Conductors               | 4 Pair  |
| Conductor Material                 | Stranded Copper   |
| Conductor Gauge                    | 28 AWG  |
| Wire Gauge (OD - mm <sup>2</sup> ) | 28  |
| Cable Length (ft.)                 | 2   |
| Cable Length (m)                   | 0.61  |
| Cable Length (in.)                 | 24  |
| Cable Length (cm)                  | 61  |
| Shipping Dimensions (hwd / in.)    | 9.00 x 7.00 x 0.50  |
| Shipping Dimensions (hwd / cm)     | 22.86 x 17.78 x 1.27  |
| Shipping Weight (lbs.)             | 0.05  |
| Shipping Weight (kg)               | 0.02  |
| <b>ENVIRONMENTAL</b>               |   |
| Operating Temperature Range        | -4° to 140°F (-20° to 60°C)                                       |
| Storage Temperature Range          | -4° to 140°F (-20° to 60°C)                                       |
| Operating Humidity Range           | 5% to 85% RH, Non-Condensing                                      |
| Storage Humidity Range             | 5% to 85% RH, Non-Condensing                                      |



Powering Business Worldwide

TRIPP LITE  
SERIES

| COMMUNICATIONS                      |  |
|-------------------------------------|--|
| Bandwidth per TIA Standard          | 250 MHz  |
| Maximum Bandwidth as Tested         | 550 MHz  |
| Network Compatibility               | 1 Gbps (Gigabit)   |
| IEEE Standards Supported            | 802.3ab; 802.3af; 802.3at  |
| FEATURES & SPECIFICATIONS           |  |
| Antibacterial                       | No   |
| IP68 Rated                          | No   |
| Snagless Connector                  | Yes  |
| STANDARDS & COMPLIANCE              |  |
| Product Certifications              | UL Listed; cUL Listed  |
| Product Compliance                  | CE (Europe); RoHS; IEEE 802.3ab 1000Base-T; IEEE 802.3af PoE; IEEE 802.3at PoE+; REACH; UKCA |
| WARRANTY & SUPPORT                  |  |
| Product Warranty Period (Worldwide) | Lifetime limited warranty  |

1000 Eaton Boulevard  
Cleveland, OH 44122  
United States  
<https://tripplite.eaton.com>

© 2024 Eaton. All Rights Reserved.  
Eaton is a registered trademark. All other trademarks  
are the property of their respective owners.