



# OmniSmart LCD 120V 650VA 350W Line-Interactive UPS, Tower, LCD display, USB port

MODEL NUMBER: OMNI650LCD











### **Highlights**

- 650VA tower 120V line interactive UPS with LCD display
- Corrects brownouts as low as 89V without using battery power
- LCD screen reports input voltage, battery charge and UPS status
- USB port, Surge-only outlets, 97% efficiency
- NEMA 5-15P input plug and 8 NEMA 5-15R outlets

## **Package Includes**

- OMNI650LCD UPS System
- Instruction manual

#### **Description**

OMNI650LCD Line-Interactive Digital UPS System offers voltage regulation, surge suppression and longlasting battery support for personal computers, home entertainment systems and media centers. Internal UPS circuits support entry-level PCs for up to 40 min. or individual VCR/DVR components for as long as two hours during power failures. Prevents data loss, viewing interruptions, lost recordings and loss of component programming. Automatic Voltage Regulation (AVR) circuits regulate brownouts as low as 89V back to usable levels without consuming battery power. Offers complete power protection in an attractive black tower configuration. Includes four battery-supported/surge-protected outlets, plus four additional surge-suppression-only outlets for items not requiring battery support. USB port enables optional unattended system shutdown without data loss in case of extended power failure. PowerAlert® software available via free download. HID-compliant USB interface enables integration with built-in power management and auto shutdown features of Windows and macOS. Built-in audible alarm and large LCD front-panel voltage display indicates line power status, battery power status, battery low/replace status and voltage boost operation. The LCD display includes a dimmer switch and can be rotated for easy viewing in any application. 650VA/350W power handling ability supports entry-level PCs, home entertainment systems, network workstations and audio/video components. Offers 3.2 minutes battery runtime with a full load of 650VA/350W and 12 minutes with a half load of 325VA/175W. Supports user battery replacement via built-in access panel.

#### **Features**

- LCD Display indicates input voltage, battery capacity and a variety of operating conditions. LCD Display
  includes a dimmer switch and is rotatable for easy viewing with UPS in either vertical or horizontal
  position.
- OMNI650LCD Digital Uninterruptible Power Supply offers voltage regulation, surge suppression and long-lasting battery support during blackouts
- Supports entry-level PCs up to 40 min. or single VCR/DVR components for up to 2 hours during blackouts
- Regulates brownouts as low as 89V back to usable levels without consuming battery power
- · 4 UPS battery-supported/surge-protected outlets plus 4 additional surge suppression-only outlets
- USB port enables data-saving unattended shutdown when used with PowerAlert software, available via FREE download from tripplite.eaton.com/products/power-alert
- HID-compliant USB port enables integration with built-in power management and auto shutdown features of Windows and macOS
- 650VA/350W power handling ability supports a variety of sensitive computer, home theater and other equipment





- 3.2 min. full load runtime (650VA/350W), 12 min. half-load runtime (325VA/175W)
- Cabinet adapts to tower format or rack-mount shelf format. rack-mount (2U) format requires an optional shelf, available separately
- Supports battery replacement via built-in access panel
- Optional PDUB15 bypass PDU enables hot-swappable UPS replacement with no disruption to connected equipment
- \$200,000 Ultimate Lifetime Insurance (U.S., Canada, and Puerto Rico only)

# **Specifications**

OVERVIEW		
UPC Code	037332126139	
UPS Type	Line-Interactive	
INPUT		
Input Phase	Single-Phase	
Rated input current (Maximum Load)	12A	
Nominal Input Voltage(s) Supported	120V AC	
UPS Input Connection Type	5-15P; Right-Angled	
UPS Input Cord Length (ft.)	6	
UPS Input Cord Length (m)	1.8	
Recommended Electrical Service	15A 120V	
OUTPUT		
Output Capacity (VA)	650	
Output Capacity (kVA)	0.65	
Output Capacity (Watts)	350	
Output Capacity (kW)	0.35	
Nominal Voltage Details	115v nominal output in battery mode	
Frequency Compatibility	60 Hz	
Output Voltage Regulation (Battery Mode)	+/- 5%	
UPS Output Receptacles (Surge Suppression Only)	4 UPS outlets, 4 surge-only outlets	
Hot-Swap PDU options	PDUB15 (2U / 8 5-15R outlets)	
Output AC Waveform (AC Mode)	Sine wave	
Output AC Waveform (Battery Mode)	PWM sine wave	
Nominal Output Voltage(s) Supported	110V; 115V; 120V	
Output Receptacles	(8) 5-15R	





Individually Controllable Load Banks	No	
BATTERY		
Battery Type	Valve Regulated Lead Acid (VRLA)	
Runtime Full Load (min.)	3.2 min. (350W)	
Runtime Half Load (min.)	12 min. (175W)	
Expandable Runtime	No	
DC System Voltage (VDC)	12	
Battery Recharge Rate (Included Batteries)	Less than 20 hours from 10 to 90%	
Battery Access	Battery access door	
Internal UPS Replacement Battery Cartridge	<a class="productLink" href="//tripplite.eaton.com/UPS-Replacement-Battery-Cartridge-Tripp-Lite-APC-Belkin-Best-Powerware-Liebert-other-UPS~RBC51">RBC51</a>	
Battery Replacement Description	Hot-swappable, user replaceable batteries	
VOLTAGE REGULATION		
Voltage Regulation Description	Automatic voltage regulation (AVR) maintains line power operation with input voltage as low as 89	
Undervoltage Correction	Input voltages between 89 and 104 are boosted by 14%	
USER INTERFACE, ALERTS & CONTROLS		
Front Panel LCD Display	Backlighted LCD screen indicates input voltage, 5-bar battery charge level, overload, AVR, on battery and replace battery status; LCD screen rotates for rack/tower viewing	
Switches	2 Switches control off/on power status and alarm-cancel/self-test operation; dimmer switch controls LCD brightness	
Alarm Cancel Operation	Power-fail alarm can be silenced using alarm-cancel switch; once silenced, alarm will re-sound to indicate low-battery status	
Audible Alarm	Audible alarm indicates power-failure and low-battery status; alarm can be disabled using PowerAlert software	
LED Indicators	Front panel LCD display	
SURGE / NOISE SUPPRESSION		
UPS AC Suppression Joule Rating	480	
UPS AC Suppression Response Time	Instantaneous	
PHYSICAL		
Primary Form Factor	Tower	
Cooling Method	Convection	
Installation Form Factors Supported with Included Accessories	Tower; Ultra-compact desktop	
Primary UPS Depth (mm)	183	
Primary UPS Height (mm)	305	
Primary UPS Width (mm)	94	





Shipping Dimensions (hwd / in.)	4.70 x 15.50 x 10.40	
Shipping Dimensions (hwd / cm)	11.94 x 39.37 x 26.42	
Shipping Weight (lbs.)	13.57	
Shipping Weight (kg)	6.16	
UPS Housing Material	ABS	
UPS Power Module Dimensions (hwd, cm)	30.48 x 9.40 x 18.29	
UPS Power Module Dimensions (hwd, in.)	12 x 3.7 x 7.2	
UPS Power Module Weight (kg)	7.03	
UPS Power Module Weight (lbs.)	15.5	
Unit Dimensions (hwd / in.)	4.700 x 3.660 x 7.240	
Unit Weight (lbs.)	13.575	
Unit Weight (kg)	6.16	
ENVIRONMENTAL		
Operating Temperature Range	32° to 104°F (0° to 40°C)	
Storage Temperature Range	5° to 122°F (-15° to 50°C)	
Relative Humidity	0 to 95%, non-condensing	
AC Mode BTU / Hr. (Full Load)	31	
AC Mode Efficiency Rating (100% Load)	97%	
Battery Mode Heat Dissipation (BTU/Hr) @ Full Load	442	
COMMUNICATIONS		
PowerAlert Software	For local monitoring via the UPS's built-in communication ports, download PowerAlert software at https://tripplite.eaton.com/products/power-alert	
Communications Cable	User supplies USB cable	
WatchDog Compatibility	Supports Watchdog application, OS and hard-reboot restart options for remote applications	
Network UPS Tools (NUT) Compatibility	NUT compatible. See a full list of NUT compatible Tripp Lite UPS systems at https://networkupstools.org/stable-hcl.html?manufacturer=Tripp%20Lite	
Network Management Card Description	Network management not supported	
Communications Interface	USB (HID enabled)	
LINE / BATTERY TRANSFER		
Transfer Time	4 milliseconds	
Low Voltage Transfer to Battery Power (Setpoint)	89	
High Voltage Transfer to Battery Power (Setpoint)	139	





FEATURES & SPECIFICATIONS			
Cold Start (Startup in Battery Mode During a Power Failure)	Cold-start operation supported		
High Availability UPS Features	Automatic Voltage Regulation (AVR); Hot swappable batteries; Surge/noise protection		
Green Energy-Saving Features	Greater than 95% efficiency - GREEN UPS		
APPLICATIONS			
UPS Applications	Home/Office Desktop; Audio/Video; Retail/Point of Sale; Hospitality		
STANDARDS & COMPLIANCE			
Product Certifications	CSA (Canada); NOM (Mexico); UL 1778		
Product Compliance	RoHS; FCC Part 15 Class B (USA)		
WARRANTY & SUPPORT			
Product Warranty Period (Worldwide)	3-year limited warranty		
Product Warranty Period (U.S. & Canada)	3-year limited warranty		
Product Warranty Period (Latin America)	3-year limited warranty		
Product Warranty Period (International)	2-year limited warranty		
Product Warranty Period (Mexico)	3-year limited warranty		
Connected Equipment Insurance (U.S., Canada & Puerto Rico)	\$200,000 <a class="insuranceLink" href="//tripplite.eaton.com/support/insurance-policy">Ultimate Lifetime Insurance</a>		

1000 Eaton Boulevard Cleveland, OH 44122 United States https://tripplite.eaton.com © 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark. All other trademarks

are the property of their respective owners.