



2-Port DB9 (RS-232) Serial PCI Card with 16550 UART, Low Profile

MODEL NUMBER: PCI-D9-02-LP







Adds 2 DB9 serial ports to your PCI computer or server or replaces existing DB9 ports. Low-profile bracket is designed for shorter computer cases.

Description

The PCI-D9-02-LP 2-Port DB9 Serial PCI Card adds two DB9 serial ports to your computer or server. By adding the PCI-D9-02-LP to a computer with no DB9 ports or not enough of them, you can upgrade your DB9 capability without having to buy a new computer.

Perfect for home or office, the PCI-D9-02-LP supports data transfer rates up to 115.2 Kbps on each port. It easily installs inside your computer in just a few minutes. The low-profile bracket's interface is compatible with universal 3.3V and 5V 32-bit PCI/PCI-X slots. Allow the appropriate drivers to automatically install on your hard drive (a driver CD is included if they don't), and connect DB9 serial extension cables (such as P520-006) to the card's DB9 connectors.

The PCI-D9-02-LP is fully compliant with PCI Local Bus Specification Revision 2.3 and compatible with industrial standard 16550 UART. On-chip 256-byte depth FIFO in transmit and receive paths of each port. Supports hardware and software flow control; PCI IRQ sharing and PCI power management; 5-, 6-, 7-, 8- and 9-bit serial formats; Even, Odd, None, Space and Mark parity; and 1- or 2-stop bit operation.

Features

Adds 2 DB9 (RS-232) Serial Ports to Your Computer

- Upgrades your DB9 capability without buying a new computer or server
- Each port supports data transfer rates up to 115.2 Kbps
- · Perfect for home or office use
- Low-profile bracket to fit shorter cases

Easy to Install Inside Your Computer

- Compatible with universal 3.3V and 5V 32-bit PCI/PCI-X slots
- Appropriate drivers install to your hard drive automatically

Loaded with the Latest Features

- Complies with PCI Local Bus Specification Revision 2.3
- Compatible with industrial standard 16550 UART
- On-chip 256-byte depth FIFO in transmit and receive paths of each port
- Supports hardware and software flow control

Highlights

- Each port supports data transfer rates up to 115.2 Kbps
- Complies with PCI Local Bus Specification Revision 2.3
- Compatible with universal 3.3V and 5V 32-bit PCI/PCI-X slots
- Compatible with industrial standard 16550 UART
- Works with Windows® and Linux®

System Requirements

- Computer with available universal 3.3V and 5V 32-bit PCI/PCI-X slot
- Windows (XP and later) or Linux (2.6.x and later)

Package Includes

- PCI-D9-02-LP 2-Port DB9 Serial PCI Card with 16550 UART, Low Profile
- Driver CD
- · Owner's manual





- Supports PCI IRQ sharing and PCI power management
- Supports 5-, 6-, 7-, 8- and 9-bit serial formats
- Supports Even, Odd, None, Space and Mark parity
- Supports 1- or 2-stop bit operation

Specifications

| OVERVIEW | |
|--|-------------------------|
| UPC Code | 037332193698 |
| | |
| CONNECTIONS | |
| Number of Ports | 2 |
| PHYSICAL | |
| Color | Red |
| Cable Length (ft.) | 0 |
| Cable Length (m) | 0.00 |
| Shipping Dimensions (hwd / in.) | 1.00 x 5.00 x 5.80 |
| Shipping Dimensions (hwd / cm) | 2.54 x 12.70 x 14.73 |
| Shipping Weight (lbs.) | 0.20 |
| Shipping Weight (kg) | 0.09 |
| STANDARDS & COMPLIANCE | |
| Product Compliance | RoHS |
| WARRANTY & SUPPORT | |
| Product Warranty Period (Worldwide) | 2-year limited warranty |

1000 Eaton Boulevard Cleveland, OH 44122 United States https://tripplite.eaton.com © 2024 Eaton. All Rights Reserved. Eaton is a registered trademark. All other trademarks are the property of their respective owners.