

## Smart Pro Line Interactive Rack/Tower UPS - NAFTA assembled version of SMART1000RM2U

MODEL NUMBER: **SM1000RMNAFTA**



### Description

1000VA line interactive UPS for server, network and telecommunications equipment/1U rackmount form factor/Corrects brownouts and overvoltages from 83 to 147/Sine wave output in both AC and battery mode/Uninterruptible Power Supply (UPS) maintains battery derived AC output during blackouts and severe voltage fluctuations/NEMA 5-15P input plug/Network-grade AC surge and noise suppression/Network management interfaces includes USB port, DB9 serial port and SNMPWEBCARD slot/Supports simultaneous detailed monitoring of equipment load levels, self-test data and mains power conditions via all 3 network interfaces at once/Includes PowerAlert monitoring software and complete cabling/Emergency Power Off (EPO) interface/Integrated 2 bank switched PDU/3 stage metered current monitoring and battery charge LEDs/Mains power and voltage regulation LEDs/Audible alarm/Self-test/Supports 2 or 4 post rackmount installation/Field replaceable, hot swappable internal batteries/Attractive all-black UPS design/Two year warranty with \$250,000 Ultimate Lifetime Insurance/Extended warranty and service contracts available.

### Features

- 1000VA/640 watt output power capacity compatible with North American 120V/60Hz power
- 1U rackmount UPS installs in standard 2 or 4 post 19 inch racks with a depth of only 16.75 inches
- Protects sensitive networking equipment from blackouts, voltage fluctuations and transient surges
- Regulation (AVR) corrects inputs from 83-147VAC back to usable 120V levels without consuming battery power
- Line interactive Automatic Voltage Regulation (AVR) corrects inputs from AVR circuits boost undervoltages by 14% depending on the severity and reduces overvoltages by 12%
- Network interfaces support simultaneous communications via USB, DB9 serial and SNMPWEBCARD slot
- Included PowerAlert UPS monitoring software supports safe unattended shutdown, monitoring and control via local connected servers, plus any number of additional servers over IP
- Communications ports support on-battery, low-battery, power-restored, AC-voltage, DC-voltage, output current monitoring, battery charge current, battery capacity, internal UPS temperature, AC line frequency, timed inverter shutoff, activate self-test and load bank output power control

### Highlights

- 1000VA / 1kVA line interactive 1U rackmount UPS
- Maintains sine-wave 120V nominal output over an input range of 83 to 147V
- Network communications supported via USB port, serial port, SNMP/Web card slot and EPO interface
- Current monitoring and switched PDU control via 2 single-outlet load banks
- Input: NEMA 5-15P (120V 15A) / Output: 6 NEMA 5-15R (120V)
- 2 year product warranty / \$250,000 Ultimate Lifetime Insurance (USA, Puerto Rico & Canada only)

### Package Includes

- SM1000RMNAFTA UPS System
- Mounting hardware
- Cabling for USB & DB9 monitoring and EPO switching
- PowerAlert unattended shutdown and UPS/Power monitoring software
- Warranty information and instruction manual



Powering Business Worldwide



- Built in Emergency Power Off (EPO) interface with cable
- Sine wave output in AC and battery modes
- Half load runtime of 15 minutes (500VA/320 watts)/Full load runtime of 7 minutes (1000VA/640 watts)
- Includes 6 NEMA 5-15R output receptacles arranged in 2 switchable single-outlet load banks
- Integrated 2 bank switched PDU enables remote outlet management for load shedding or remote reboot of individual devices
- 3 stage metered LEDs offer current monitoring and battery charge level
- Mains power and voltage regulation LEDs offer at-a-glance power status information
- Front panel switches support self-test and alarm cancel functions
- UPS ships fully assembled in full compliance with DOT regulations, no time consuming connection of internal batteries by user required
- UL (USA), cUL (Canada), NOM (Mexico), FCC Class A (Emissions) listed
- 2 year manufacturer's product warranty, \$250,000 Ultimate Lifetime Insurance

## Specifications

OVERVIEW	
UPC Code	037332137487
INPUT	
Rated input current (Maximum Load)	9.2A
Nominal Input Voltage(s) Supported	120V AC
UPS Input Connection Type	5-15P
Input Circuit Breakers	15A
UPS Input Cord Length (ft.)	10
UPS Input Cord Length (m)	3.1
Recommended Electrical Service	15A 120V
Input Cord Length (ft.)	10
Input Cord Length (m)	3.05
OUTPUT	
Output Capacity (VA)	1000
Output Capacity (kVA)	1
Output Capacity (Watts)	640
Power Factor	0.6
Frequency Compatibility	60 Hz
Output Voltage Regulation (Line Mode)	-21%, +8%
Output Voltage Regulation (Battery Mode)	+/- 5%
Load Management Receptacles	Two switchable two-outlet 5-15R load banks

Output AC Waveform (AC Mode)	Sine wave
Output AC Waveform (Battery Mode)	Pure Sine wave
Nominal Output Voltage(s) Supported	120V
Output Receptacles	(6) 5-15R
<b>BATTERY</b>	
Runtime Full Load (min.)	7 min. (640w)
Runtime Half Load (min.)	15 min. (320w)
DC System Voltage (VDC)	24
Battery Recharge Rate (Included Batteries)	Less than 4 hours from 10% to 90%
Battery Access	Front panel battery access door
Internal UPS Replacement Battery Cartridge	&nbsp;<a class="productLink" href="//www.tripplite.com/1U-UPS-Replacement-24VDC-Battery-Cartridge-1-Set-4-for-Select-Tripp-Lite-SmartPro-UPS-RBC64-1U">RBC64-1U</a>&nbsp;
Battery Replacement Description	Hot-swappable, user replaceable batteries
<b>VOLTAGE REGULATION</b>	
Voltage Regulation Description	Automatic voltage regulation (AVR) maintains line power operation with an input voltage range of 83 to 147
Overvoltage Correction	Input voltages between 128 and 147 are reduced by 12%
Undervoltage Correction	Input voltages between 83 and 107 are boosted by 14%
<b>USER INTERFACE, ALERTS &amp; CONTROLS</b>	
Switches	2 Switches control off/on power status and alarm-cancel/self-test operation
Alarm Cancel Operation	Power-fail alarm can be silenced using alarm-cancel switch; once silenced, alarm will re-sound to indicate low-battery status
Audible Alarm	Audible alarm indicates power-failure, overload and low-battery conditions
LED Indicators	5 LEDs indicate line power, battery power, overload, voltage regulation and battery low/replace status
<b>SURGE / NOISE SUPPRESSION</b>	
UPS AC Suppression Joule Rating	480
EMI / RFI AC Noise Suppression	Yes
AC Suppression Joule Rating	480
AC Suppression Response Time	Instantaneous
<b>PHYSICAL</b>	
Primary Form Factor	Rackmount
Rack Height	1U
Cooling Method	Fan

Included Mounting Accessory Description	Adjustable mounting rail kit included
Primary UPS Depth (mm)	427
Primary UPS Height (mm)	43
Primary UPS Width (mm)	445
Shipping Dimensions (hwd / in.)	9.00 x 24.00 x 20.25
Shipping Dimensions (hwd / cm)	22.86 x 60.96 x 51.44
Shipping Weight (lbs.)	41.50
Shipping Weight (kg)	18.82
UPS Housing Material	Steel
UPS Power Module Dimensions (hwd, cm)	4.32 x 44.45 x 42.67
UPS Power Module Dimensions (hwd, in.)	1.7 x 17.5 x 16.8
UPS Power Module Weight (kg)	14.51
UPS Power Module Weight (lbs.)	32
<b>ENVIRONMENTAL</b>	
Operating Temperature Range	+32 to +104 degrees Fahrenheit / 0 to +40 degrees Celsius
Storage Temperature Range	+5 to +122 degrees Fahrenheit / -15 to +50 degrees Celsius
Relative Humidity	0 to 95%, non-condensing
AC Mode BTU / Hr. (Full Load)	138.9
AC Mode Efficiency Rating (100% Load)	94%
Battery Mode Heat Dissipation (BTU/Hr) @ Full Load	477.7
<b>COMMUNICATIONS</b>	
Network Monitoring Port Description	Supports detailed monitoring of UPS and site power conditions
PowerAlert Software	Included
Communications Cable	USB and DB9 cabling included
WatchDog Compatibility	Supports Watchdog application, OS and hard-reboot restart options for remote applications
Communications Interface	USB; DB9 Serial; EPO (emergency power off); Slot for SNMP/Web interface
<b>LINE / BATTERY TRANSFER</b>	
Transfer Time	2-4 milliseconds
Low Voltage Transfer to Battery Power (Setpoint)	83
High Voltage Transfer to Battery Power (Setpoint)	147



Powering Business Worldwide



FEATURES & SPECIFICATIONS	
Cold Start (Startup in Battery Mode During a Power Failure)	Cold-start operation supported
High Availability UPS Features	Hot swappable batteries
Green Energy-Saving Features	Individually controllable load banks
Grounding Details	Back panel grounding lug
WARRANTY & SUPPORT	
Product Warranty Period (Worldwide)	2-year limited warranty
Connected Equipment Insurance (U.S., Canada & Puerto Rico)	\$250,000&nbsp;<a class="insuranceLink" href="//www.tripplite.com/support/insurance-policy">Ultimate Lifetime Insurance</a>&nbsp;

1000 Eaton Boulevard  
 Cleveland, OH 44122  
 United States  
<https://tripplite.eaton.com>

© 2024 Eaton. All Rights Reserved.  
 Eaton is a registered trademark. All other trademarks  
 are the property of their respective owners.