



# Smart Pro Line Interactive Tower UPS System - NAFTA assembled version of the SMART1500

# MODEL NUMBER: SM1500NAFTA





## Description

Tripp Lite's SM1500NAFTA intelligent, line interactive UPS system protects servers, networking accessories and telecommunications equipment from blackouts, voltage fluctuations and transient surges. Large internal batteries offer 20 minutes half load runtime and 7 minutes at full load during power failures. 1500VA/980 watt power handling capability supports a variety of networking, telecom and various other application types, including the support of multiple network workstations. Includes a total of 6 outlets, 1 of which can be individually powered on and off via software interface to selectively reboot remote equipment or to automatically shed less significant loads to extend battery runtime for more critical equipment. Supports remote monitoring of UPS and site power conditions via built-in USB and DB9 monitoring ports. Includes PowerAlert UPS monitoring and unattended shutdown software with complete cabling. Built-in audible alarm and 5 front panel LEDs indicate status of line power, battery power, battery low/replace, voltage regulation and load level. Wall mountable with optional UPSWM wallmount bracket. Network-grade AC surge suppression protects equipment from damage and performance problems resulting from transient surges. Attractive, small-footprint tower housing uses less than 66 square inches of floor or desktop space. \$250,000 connected equipment insurance (USA and Canada Only).

#### **Features**

- 1500VA/980 watt power handling capability supports a variety of networking, telecom and various other application types
- Built-in voltage regulation and battery support, plus complete AC suppression prevents equipment damage, data loss and downtime
- Large internal batteries offer 20 minutes half load runtime and 7 minutes at full load during power failures
- Automatic Voltage Regulation (AVR) circuits with two boost and one voltage reduction level maintains usable 120V nominal output over an input voltage range of 75-147V
- Includes a total of 6 NEMA5-15R outlets, 1 of which can be individually powered on and off via software interface to selectively reboot remote equipment or shed less significant loads to extend battery runtime for more critical equipment
- Includes 1 USB and 1 DB9 monitoring port for remote monitoring of UPS status and site power conditions

### **Highlights**

- 1500VA / 1.5kVA line interactive tower UPS
- Maintains 120V nominal output over an input range of 75 to 147V
- Network communications supported via USB port, serial port
- Input: NEMA 5-15P (120V 15A) / Output: 6 NEMA 5-15R (120V)
- \$250,000 Ultimate Lifetime Insurance (USA, Puerto Rico and Canada only)

#### **Package Includes**

- SM1500NAFTA UPS System
- USB and DB9 monitoring cables
- PowerAlert unattended shutdown and UPS/Power monitoring software
- Instruction manual with warranty information





- Communications ports enable safe unattended shutdown without data loss during extended power failures
- Communications ports support messaging of UPS and line power status, including on-battery, lowbattery, power-restored, AC line voltage, DC battery voltage and battery capacity
- Communications ports support timed inverter shutoff after unattended shutdown, activate self-test and 10 second reboot of connected equipment
- PowerAlert UPS monitoring and unattended shutdown software with complete cabling included
- Supports Tripp Lite's WatchDog software application to restore unresponsive programs by automatically
  restarting them and rebooting completely locked computers by automatically switching UPS power off
  and back on again
- Notification of system status via 5 LEDs and multi-function audible alarms
- Wall mountable with UPSWM wallmount bracket
- Attractive small footprint beige tower housing uses less than 66 square inches
- · Hot-swappable/user replaceable batteries allow on-site battery replacement
- · Cold start capability enables UPS turn-on in battery mode during blackout conditions
- UL (USA), cUL (Canada), NOM (Mexico), Class A (Emissions)
- \$250,000 Ultimate Lifetime Insurance (USA and Canada only)
- \$250,000 connected equipment insurance (USA and Canada Only)

# **Specifications**

OVERVIEW		
UPC Code	037332137678	
INPUT		
Rated input current (Maximum Load)	12A	
Nominal Input Voltage(s) Supported	120V AC	
UPS Input Connection Type	5-15P	
Input Circuit Breakers	15A	
UPS Input Cord Length (ft.)	6	
UPS Input Cord Length (m)	1.8	
Recommended Electrical Service	15A 120V	
OUTPUT		
Output Capacity (VA)	1500	
Output Capacity (kVA)	1.5	
Output Capacity (Watts)	980	
Power Factor	0.7	
Frequency Compatibility	60 Hz	
Output Voltage Regulation (Line Mode)	-18%, +8%	
Output Voltage Regulation (Battery Mode)	+/- 5%	



Cooling Method

Fan



Load Management Receptacles	One switchable single-outlet 5-15R load bank
Output AC Waveform (AC Mode)	Sine wave
Output AC Waveform (Battery Mode)	PWM sine wave
Nominal Output Voltage(s) Supported	120V
Output Receptacles	(6) 5-15R
BATTERY	
Runtime Full Load (min.)	7 min. (980w)
Runtime Half Load (min.)	20 min. (490w)
DC System Voltage (VDC)	36
Battery Recharge Rate (Included Batteries)	Less than 4 hours from 10% to 90%
Battery Access	Battery access door
Internal UPS Replacement Battery Cartridge	<a class="productLink" href="//www.tripplite.com/UPS-Replacement-Battery-Cartridge-Kit-select-Tripp-Lite-&lt;br&gt;Best-Powerware-Liebert-other-UPS~RBC53">RBC53</a>
Battery Replacement Description	Hot-swappable, user replaceable batteries
VOLTAGE REGULATION	
Voltage Regulation Description	Automatic voltage regulation (AVR) maintains line power operation with an input voltage range of 75 to 147
Overvoltage Correction	Input voltages between 128 and 147 are reduced by 12%
Undervoltage Correction	Input voltages between 93 and 107 are boosted by 14%
Severe Undervoltage Correction	Input voltages between 75 and 92 are boosted by 30%
USER INTERFACE, ALERTS & COM	NTROLS
Switches	2 Switches control off/on power status and alarm-cancel/self-test operation
Alarm Cancel Operation	Power-fail alarm can be silenced using alarm-cancel switch; once silenced, alarm will re-sound to indicate low- battery status
Audible Alarm	Audible alarm indicates power-failure, overload and low-battery conditions
LED Indicators	5 LEDs indicate line power, battery power, overload, voltage regulation and battery low/replace status
SURGE / NOISE SUPPRESSION	
UPS AC Suppression Joule Rating	480
UPS AC Suppression Response Time	Instantaneous
EMI / RFI AC Noise Suppression	Yes
PHYSICAL	
Primary Form Factor	Tower





Installation Form Factors Supported with Included Accessories	Tower
Installation Form Factors Supported with Optional Accessories	Wallmount ( <a class="productLink" href="//www.tripplite.com/Wall-Mount-Bracket-Installation-Accessories-&lt;br&gt;for-UPS-Systems~UPSWM">UPSWM</a> - tower mounting kit)
Primary UPS Depth (mm)	229
Primary UPS Height (mm)	325
Primary UPS Width (mm)	191
Shipping Dimensions (hwd / in.)	18.25 x 12.00 x 13.75
Shipping Dimensions (hwd / cm)	46.36 x 30.48 x 34.92
Shipping Weight (lbs.)	42.60
Shipping Weight (kg)	19.32
UPS Housing Material	PVC
UPS Power Module Dimensions (hwd, cm)	32.51 x 19.05 x 22.86
UPS Power Module Dimensions (hwd, in.)	12.8 x 7.5 x 9
UPS Power Module Weight (kg)	17.42
UPS Power Module Weight (lbs.)	38.4
ENVIRONMENTAL	
Operating Temperature Range	+32 to +104 degrees Fahrenheit / 0 to +40 degrees Celsius
Storage Temperature Range	+5 to +122 degrees Fahrenheit / -15 to +50 degrees Celsius
Relative Humidity	0 to 95%, non-condensing
AC Mode BTU / Hr. (Full Load)	138.8
AC Mode Efficiency Rating (100% Load)	96%
Battery Mode Heat Dissipation (BTU/Hr) @ Full Load	454.4
COMMUNICATIONS	
Network Monitoring Port Description	Supports detailed monitoring of UPS and site power conditions
PowerAlert Software	Included
Communications Cable	USB and DB9 cabling included
WatchDog Compatibility	Supports Watchdog application, OS and hard-reboot restart options for remote applications
Communications Interface	USB; DB9 Serial
LINE / BATTERY TRANSFER	
Transfer Time	2-4 milliseconds
Low Voltage Transfer to Battery Power (Setpoint)	75





High Voltage Transfer to Battery Power (Setpoint)	147		
FEATURES & SPECIFICATIONS			
Cold Start (Startup in Battery Mode During a Power Failure)	Cold-start operation supported		
High Availability UPS Features	Hot swappable batteries		
Green Energy-Saving Features	Greater than 95% efficiency - GREEN UPS; Individually controllable load banks		
WARRANTY & SUPPORT			
Product Warranty Period (Worldwide)	2-year limited warranty		
Connected Equipment Insurance (U.S., Canada & Puerto Rico)	\$250,000 <a class="insuranceLink" href="//www.tripplite.com/support/insurance-policy">Ultimate Lifetime Insurance</a>		

1000 Eaton Boulevard Cleveland, OH 44122 United States https://tripplite.eaton.com © 2024 Eaton. All Rights Reserved. Eaton is a registered trademark. All other trademarks are the property of their respective owners.