

Protect It! 1-Outlet Surge Protector, Direct Plug-In, 350 Joules, Timer Selection Switch

MODEL NUMBER: SK10TG



Highlights

- 1 outlets/direct plug-in
- 350 joule rating
- Timer selection switch for 1, 3, or 6 hours
- Diagnostic LEDs

Package Includes

- SK10TG surge suppressor
- Instruction sheet

Description

The SK10TG surge suppressor with timer offers reliable surge and line noise protection. The compact direct plug-in design allows for easy portability and features 1 outlet and 350 joules of surge energy absorption. Timer selection switch for 1, 3, or 6 hours helps make connected devices more energy efficient. On/Off push button lets you shut off outlet at any time. Diagnostic LEDs alert you to potential wiring or protection faults before connected equipment is damaged. \$5,000 Ultimate Lifetime Insurance (U.S., Canada, and Puerto Rico only).

Features

- 1 outlets / direct plug-in
- Surge suppression rating: 350 joules
- Timer Feature
- EMI/RFI noise filtering
- Diagnostic LEDs indicate Protected (green) & Grounded (red)
- \$5,000 Ultimate Lifetime Insurance (U.S., Canada, and Puerto Rico only)

Specifications

OVERVIEW	
UPC Code	037332177018
INPUT	
Nominal Input Voltage(s) Supported	120V AC
Recommended Electrical Service	120V
Input Cord Length Details	Direct Plug-In
Voltage Compatibility (VAC)	120



Powering Business Worldwide

TRIPP-LITE
by **EAT•N**

Input Plug Type	NEMA 5-15P
Input Cord Length (ft.)	0
Right-Angle Plug	No
Input Cord Length (m)	0.00
Integrated Cord Clip	No
OUTPUT	
Frequency Compatibility	50 / 60 Hz
Output Receptacles	(1) 5-15R
Circuit Breaker (amps)	15
Transformer Accommodation	(1) Yes
Right-Angle Outlets	No
USER INTERFACE, ALERTS & CONTROLS	
Diagnostic LED(s)	Yes
SURGE / NOISE SUPPRESSION	
AC Suppression Joule Rating	350
AC Suppression Response Time	< 1ns
Protection Modes	Includes full normal mode (H-N) and common mode (N-G / H-G) line suppression
AC Suppression Surge Current Rating	27,000
UL1449 Let Through Rating	500, 400, 500
EMI / RFI Filtering	Yes
Automatic Shut-Off	No
DATALINE SURGE SUPPRESSION	
Cable (Coax) Protection	No
Network (Ethernet) Protection	No
Telephone/DSL Protection	No
PHYSICAL	
Material of Construction	Plastic
Mounting Holes or Slots	No
Receptacle Color	Black
Shipping Dimensions (hwd / in.)	3.80 x 2.60 x 2.90
Shipping Dimensions (hwd / cm)	9.65 x 6.60 x 7.37
Shipping Weight (lbs.)	0.30

Shipping Weight (kg)	0.14
Unit Dimensions (hwd / in.)	2.760 x 2.760 x 1.500
Unit Dimensions (hwd / cm)	7 x 7 x 3.8
Unit Weight (lbs.)	.22
Unit Weight (kg)	0.10
FEATURES & SPECIFICATIONS	
Rotatable Outlets	No
Antimicrobial	No
STANDARDS & COMPLIANCE	
Product Certifications	UL 1449
Product Compliance	RoHS
WARRANTY & SUPPORT	
Product Warranty Period (Worldwide)	Lifetime limited warranty
Connected Equipment Insurance (U.S., Canada & Puerto Rico)	\$5,000 Ultimate Lifetime Insurance

1000 Eaton Boulevard
Cleveland, OH 44122
United States
<https://tripplite.eaton.com>

© 2024 Eaton. All Rights Reserved.
Eaton is a registered trademark. All other trademarks
are the property of their respective owners.