

Universal Reversible USB 2.0 Cable (Reversible A to B M/M), 6 ft. (1.83 m)

MODEL NUMBER: UR022-006



Reversible USB "A" connector plugs in any direction

Features

- 6ft, USB 2.0 A-Male to B-Male, with Universal / Reversible "A" connector
- USB 2.0 compliant, to 480Mbps transfer rates
- Backward compatible with previous USB generations
- Gold plated contacts and molded ends provide a lifetime of use
- 28AWG Data Pair, 24AWG Power pair

Specifications

| OVERVIEW | |
|----------------------|-------------------------|
| UPC Code | 037332179449 |
| Technology | USB 2.0 (High Speed) |
| Cable Type | Passive |
| CONNECTIONS | |
| Side A - Connector 1 | REVERSIBLE USB A (MALE) |
| Side B - Connector 1 | USB B (MALE) |
| Connector Style | Straight |
| PHYSICAL | |
| Cable Jacket Color | Black |
| Cable Length (ft.) | 6 |

Highlights

- 6-ft. (1.83 m), USB 2.0, A/B Peripheral device cable
- Universal, Reversible "A" connector allows plugging in any direction

System Requirements

- Any USB device requiring a USB cable
- USB2.0 performance only when used with USB2.0 device and USB2.0 controller

Package Includes

- Universal Reversible USB 2.0 A-Male to B-Male Device Cable - 6-ft. (1.83 m)



Powering Business Worldwide

TRIPP LITE
SERIES

| | |
|-------------------------------------|------------------------------|
| Cable Length (m) | 1.83 |
| Shipping Dimensions (hwd / in.) | 7.00 x 9.00 x 0.50 |
| Shipping Dimensions (hwd / cm) | 17.78 x 22.86 x 1.27 |
| Shipping Weight (lbs.) | 0.14 |
| Shipping Weight (kg) | 0.06 |
| ENVIRONMENTAL | |
| Operating Temperature Range | 14° to 122°F (-10° to 50°C) |
| Storage Temperature Range | 5° to 140°F (-15° to 60°C) |
| Operating Humidity Range | 0% to 90% RH, Non-Condensing |
| Storage Humidity Range | 0% to 90% RH, Non-Condensing |
| STANDARDS & COMPLIANCE | |
| Product Compliance | RoHS |
| WARRANTY & SUPPORT | |
| Product Warranty Period (Worldwide) | Lifetime limited warranty |

1000 Eaton Boulevard
Cleveland, OH 44122
United States
<https://tripplite.eaton.com>

© 2024 Eaton. All Rights Reserved.
Eaton is a registered trademark. All other trademarks
are the property of their respective owners.